

Products

[PRODUCTS](#)

ELECTRICAL

[Polaris™](#)

- [Polaris™](#)
- [Insulated Blue](#)
- [Insulated Grey](#)
- [Insulated](#)
- [Non-Insulated](#)

[Tools & Hardware](#)

[Connectors](#)

[Firestop](#)

[Grounding](#)

[Easy-Twist](#)

[Splicing](#)

[Miniterms](#)

[Switches](#)

[DataComm](#)

[Wire Management](#)

[TORK](#)

[LIGHTING](#)

[POOL & SPA PRODUCTS](#)

Email Newsletter



[Home](#) [Products](#) [Electrical](#) [Polaris™](#) [Polaris™](#) [Dual Entry w/Mtg](#) [IPLMD Series Dual Side Entry w/Mtg](#)

IPLMD Series Dual Side Entry w/Mtg



Wire entry ports on both sides of the connector allow for access from either side. Supplied with removable access plugs to close the entry port not being used. The mounting holes at each end of the connector allow for direct isolated mounting to the trough, panel or wireway. Eliminates the need for cover and taping

[Products](#) [Product Documentation](#) [Videos & How-To's](#)

SKU	UPC	Name	Weight	Qty Avail	Price
IPLMD600-4	66238178916	600 MCM - 6 AWG POLARIS INSULATED MULTI-TAP CONN 4 PORT (DUAL SIDED ENTRY & MOUNTABLE)	0.00		
IPLMD600-5	66238178917	600 MCM - 6 AWG POLARIS INSULATED MULTI-TAP CONN 5 PORT (DUAL SIDED ENTRY & MOUNTABLE)	0.00		
IPLMD600-12	66238178923	600 MCM - 6 AWG POLARIS INSULATED MULTI-TAP CONN 12 PORT (DUAL SIDED ENTRY & MOUNTABLE)	0.00		
IPLMD600-10	66238178922	600 MCM - 6 AWG POLARIS INSULATED MULTI-TAP CONN 10 PORT (DUAL SIDED ENTRY & MOUNTABLE)	0.00		
IPLMD600-8	66238178920	600 MCM - 6 AWG POLARIS INSULATED MULTI-TAP CONN 8 PORT (DUAL SIDED ENTRY & MOUNTABLE)	0.00		
IPLMD600-9	66238178921	600 MCM - 6 AWG POLARIS INSULATED MULTI-TAP CONN 9 PORT (DUAL SIDED ENTRY & MOUNTABLE)	0.00		
IPLMD600-6	66238178918	600 MCM - 6 AWG POLARIS INSULATED MULTI-TAP CONN 6 PORT (DUAL SIDED ENTRY & MOUNTABLE)	0.00		
IPLMD600-3	66238178915	600 MCM - 6 AWG POLARIS INSULATED MULTI-TAP CONN 3 PORT (DUAL SIDED ENTRY & MOUNTABLE)	0.00		
IPLMD500-7	66238194505	500 MCM - 4 AWG POLARIS INSULATED MULTI-TAP CONN 7 PORT (DUAL SIDED ENTRY & MOUNTABLE)	2.33		
IPLMD250-4	66238194302	250 MCM - 6 AWG POLARIS INSULATED MULTI-TAP CONN 4 PORT(DUAL SIDED ENTRY & MOUNTABLE)	0.71		
IPLMD750-8	66238194606	750-250 MCM NON -UL INSULATED MULTI-TAP CONN 8 PORT (DUAL SIDED ENTRY & MOUNTABLE)	4.63		
IPLMD250-10	66238194308	250 MCM - 6 AWG POLARIS INSULATED MULTI-TAP CONN 10 PORT (DUAL SIDED ENTRY & MOUNTABLE)	1.40		
IPLMD500-6	66238194504	500 MCM - 4 AWG POLARIS INSULATED MULTI-TAP CONN 6 PORT (DUAL SIDED ENTRY & MOUNTABLE)	2.07		

IPLMD350-5	66238194403	350 MCM - 6 AWG POLARIS INSULATED MULTI-TAP CONN 5 PORT (DUAL SIDED ENTRY & MOUNTABLE)	1.32			
IPLMD3/0-6	66238193224	3/0-6 AWGPOLARIS INSULATED MULTI-TAP CONN 6 PORT (DUAL SIDED ENTRY & MOUNTABLE)	0.70			
IPLMD350-12	66238194410	3/0-6 AWGPOLARIS INSULATED MULTI-TAP CONN 12PORT (DUAL SIDED ENTRY & MOUNTABLE)	2.58			
IPLMD350-8	66238194406	350 MCM - 6 AWG POLARIS INSULATED MULTI-TAP CONN 8 PORT (DUAL SIDED ENTRY & MOUNTABLE)	1.86			
IPLMD3/0-7	66238193225	3/0-6 AWGPOLARIS INSULATED MULTI-TAP CONN 7 PORT (DUAL SIDED ENTRY & MOUNTABLE)	0.80			
IPLMD350-7	66238194405	350 MCM - 6 AWG POLARIS INSULATED MULTI-TAP CONN 7 PORT (DUAL SIDED ENTRY & MOUNTABLE)	1.68			
IPLMD500-4	66238194502	500 MCM - 4 AWG POLARIS INSULATED MULTI-TAP CONN 4 PORT (DUAL SIDED ENTRY & MOUNTABLE)	1.55			

[Previous](#) [Next](#)