

GROUNDING CONNECTORS

Grounding Pigtails (for solid & stranded wire) and Grounding Clips

PG, GGC, GSH, GSC SERIES



FEATURES

SOLID PIGTAILS WITH SCREWS

- Pigtails are insulated conductors supplied with an attached ground screw on one end and the insulation stripped back one inch on the other end.
- Meets NEC requirements.

STRANDED WITH RING & SPADE

- Supplied with a spade terminal on one end and a ring terminal with a captive green-dyed screw on the other end.
- 65 strand #12 AWG and 41 strand #14 AWG for maximum flexibility.



RATINGS



All dimensional data is listed in inches.

CAT. NO.	FIG. NO.	DESCRIPTION	STD. CTN. QTY.
PG14C	1	6.5 Inch 14 AWG Solid With Combo Screw - Green	50
PG12C	1	6.5 Inch 12 AWG Solid With Combo Screw - Green	50
PG12C-8	1	8 Inch 12 AWG Solid With Combo Screw - Green	50
PG14SC	2	8 Inch 14 AWG (41W) Stranded With Combo Slotted Screw	50
PG12SC	2	8 Inch 12 AWG (65W) Stranded With Combo Slotted Screw	50
GSH	3	Hex Head Green Grounding Screw	100
GSC	3	Combo Slotted Hex Screw	100
GGC-1000	4	Green Grounding Clips	100