



Easy-Twist™ Closed End Connector 22-18

Part# C22-N

22-18 AWG Closed End Conn.-Nylon, 100/Pack

In Stock



Mouse over image for enlarged view

[Zoom](#) [Share](#)

Product Information **Documents**

Wire Type:	CU Wire Only
Type:	Closed End Connectors
Wire Size:	22-18 AWG
Material:	Nylon 66
Color:	White
Voltage Rating:	300 V
Dimensions:	H=.709 - W=.307 - ID=.102
Application:	Splicing Wire
Number Of Conductors:	1
Finish:	Nylon
Insulation:	Nylon 66
Temperature Rating:	105 C
Standard:	UL486C Listed
Environmental Conditions:	105 C

Related Products

