

# GROUND CLAMPS Heavy Duty with 360° Adapters for Rigid Conduit EG SERIES




## WITH 360° ADAPTERS FOR RIGID CONDUIT




- Bronze water pipe clamps with bronze adapters.
- Excellent quality yet economical.
- All adapters are interchangeable.
- Assembled with zinc-plated steel screws.
- Hub swings 360° for easy alignment.
- Used to connect rigid conduit and ground conductor to water pipe.
- UL Listed 467 Grounding and Bonding.


**EG-3**





**EG-4**



**EG-15**




**EG-5**




**EG-6**



**EG-7**




**EG-8**



**EG-9**



**EG-24**



All dimensional data is listed in inches.

CAT. NO.	CONDUIT HUB SIZE	PIPE SIZE (IPS)	GROUND WIRE RANGE	LENGTH (L)	WIDTH (W)	HEIGHT (H)	STD. CTN. QTY.
<b>EG-3</b>	1/2	1/2 - 1	10 SOL - 2/0 STR	2.200	0.585	2.300	20
<b>EG-4</b>	1/2	1 1/4 - 2	10 SOL - 2/0 STR	3.588	0.737	3.117	10
<b>EG-15</b>	1/2	2 1/2 - 4	10 SOL - 2/0 STR	6.125	0.972	4.834	6
<b>EG-5</b>	1/2	1/2 - 1	10 SOL - 2/0 STR	2.208	0.597	2.210	15
<b>EG-6</b>	1/2	1 1/4 - 2	10 SOL - 2/0 STR	3.631	0.725	2.696	10
<b>EG-7</b>	3/4	1/2 - 1	10 SOL - 2/0 STR	2.298	0.663	2.470	15
<b>EG-8</b>	3/4	1 1/4 - 2	10 SOL - 2/0 STR	3.576	0.789	3.841	8
<b>EG-9</b>	1	1/2 - 1	10 SOL - 3/0 STR	2.280	0.650	1.900	12
<b>EG-10</b>	1	1 1/4 - 2	10 SOL - 3/0 STR	3.587	0.792	4.029	8
<b>EG-24</b>	1	2 1/2 - 4	10 SOL - 3/0 STR	6.125	0.962	5.158	6