



Actual

**Catalog Number:** JWR  
**Product ID:** 7TAA014200R0016  
**UPC Number:** 78378643782  
**Status:** Active

Ground Rod Clamps Type - Wide Range, Rod Size 3/8 - 3/4, Wire Range 10 Sol. - 1/0 Str.

- UL listed for direct burial in earth/concrete. Constructed from bronze alloy and high performance stainless steel bolt.
- Provides wide range of connection sizes. More than 300 lbs. Torque capacity.

### North American Specifications (UNSPSC)

UNSPSC	39121613 Grounding devices or assemblies
IGCC	4909 Grounding devices or assemblies
Brand Name	Blackburn
Type	Ground Rod Clamps
Special Features	UL listed for direct burial in earth/concrete. Constructed from bronze alloy and high performance stainless steel bolt.
Conductor Material	Copper
Insulation	No

### Packaging

Inner Quantity	25
Outer Quantity	100
Outer Dimensions (inches)	6x6.5x6.5
Weight Uom	13.69 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000076

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)