

# IRWIN®

## Fast Release™ Curved Jaw Locking Pliers Features:



- Self-energizing lower jaw provides 3X more gripping power than traditional locking pliers, with no slipping or stripping.
- Provides maximum torque without requiring heavy input pressure – jaw mechanism naturally grips tighter as more torque is applied to the tool.
- One-handed, triggerless release is 2X easier to open than traditional locking pliers.
- Anti-pinch, non-slip ProTouch™ Grips provide comfort, control, and less hand fatigue.
- Curved jaw puts tremendous pressure on four points of any style nut or bolt head, making it perfect for any application that requires maximum torque.
- Constructed of high-grade heat-treated alloy steel for maximum toughness and durability.
- Hardened teeth are designed to grip from any angle.
- Hex key adjusting screw tightens to adjust pressure and draw materials together and provides a controlled release.
- Backed by the IRWIN VISE-GRIP Lifetime Guarantee.

Item # 11T



\*vs. traditional locking pliers

## Replacement Parts

Item #	Jaw Capacity	Model	Size
11T	1-7/8" / 48 mm	10CR	10" / 250 mm
13T	1-1/2" / 38 mm	7CR	7" / 175 mm
4935581	1-1/8" / 29 mm	5CR	5" / 125 mm