



38912

### Wood Installer Bits

- Hole in flute for easy wire pulling through walls, ceilings, and floors.
- Premium alloy steel construction for extended drilling life.
- Special 82° point for fast drilling and easy starts.

Diameter	Shank Size	Overall Length	Item #	Bulk Item #
1/4"	.230"	12"	—	38904
5/16"	.285"	12"	—	38905
3/8"	.370"	12"	—	38906
1/2"	.370"	12"	—	38908
9/16"	.370"	12"	—	38909
5/8"	.370"	12"	—	38910
3/4"	.370"	12"	—	38912
1/4"	.230"	18"	39104	39004
5/16"	.285"	18"	39105	39005
3/8"	.370"	18"	39106	39006
7/16"	.370"	18"	39107ZR	39007
1/2"	.370"	18"	39108ZR	39008
9/16"	.370"	18"	39109ZR	—
5/8"	.370"	18"	39110	39010
11/16"	.370"	18"	39111	—
3/4"	.370"	18"	39112	—
1/4"	.230"	24"	—	39404
5/16"	.285"	24"	—	39405
3/8"	.370"	24"	—	39406
1/2"	.370"	24"	—	39408
1/4"	.230"	30"	—	39604
3/8"	.370"	30"	—	39606
1/2"	.370"	30"	—	39608
<b>Installer Bit Sets</b>				
3-pc Set 1/4", 3/8", 1/2"	—	—	—	3044001LW



40012

### Carbide Tip Installer Bits

- Hole in flute makes it easy to pull wire through walls, ceilings, and floors.
- Specially designed flute quickly clears masonry dust.
- Heavy duty 118° point enters material quickly.
- Carbide tip and cutting edge is ideal for use where masonry construction is encountered, including brick, mortar joints, and cinder blocks.

Diameter	Shank Size	Overall Length	Bulk Item #
1/4"	.245"	18"	40004ZR
5/16"	.250"	18"	40005
3/8"	.370"	18"	40006
1/2"	.370"	18"	40008
5/8"	.370"	18"	40010
3/4"	.370"	18"	40012



45002

### Adjustable Wood Bits

- Adjustable cutting blade bores a variety of hole sizes (Cuts 19 hole sizes in increments of 1/8").
- Lockhead screw securely holds blade at desired drilling diameter.

Diameter	Shank Size	Usage	Overall Length	Item #
5/8" - 1-3/4"	9/32"	Drill Press / Hand Brace	5-1/2"	44801
7/8" - 3"	11/32"	Drill Press / Hand Brace	6-1/2"	45002
7/8" - 3"	—	Hand Brace	6-1/2"	44202