



SPECIFICATIONS

PRODUCT NUMBER	PRODUCT DIMENSIONS				POWER TOOL TYPE	RPM MAX
	DIAMETER	THICKNESS	ARBOR	OPTIONAL ARBOR ADJUSTMENT		
1972914	1.5"	.050"	3/8"	1/4"	Die Grinder	40200
1972917	2"	.050"	3/8"	1/4"	Die Grinder	30500
1972918	3"	.050"	3/8"	1/4"	Die Grinder	20300
1972919	4"	.050"	3/8"	1/4"	Die Grinder	15200
1972920	4"	.050"	5/8"		Angle Grinder	15200
1972921	4.5"	.050"	7/8"		Angle Grinder	13300
1972922	5"	.050"	7/8"		Angle Grinder	12200
1972923	6"	.050"	7/8"	Diamond Knock Out	Angle Grinder/Circular Saw	10100
1972924	7"	.060"	7/8"	Diamond Knock Out	Angle Grinder/Circular Saw	8400
1972925	8"	.060"	5/8"	Diamond Knock Out	Circular Saw	7600
1972926	10"	.100"	5/8"		Stationary/Small Chop Saw	5900
1972927	12"	.130"	1"		Chop Saw	5000
1972929	14"	130"	1"		Chop Saw	4300
1972930	12"	150"	1"	20mm	Gas Saw	6200
1972932	14"	150"	1"	20mm	Gas Saw	5300