

Detailed Specifications

[SSL Secure Online Payment Processing](#)

 Live help is offline...



- [Description](#)
- [Specification](#)
- [Reviews \(0\)](#)

Voltage: 34V, Wattage: 100W, Type: A19 Light Bulb, Length: 4.10 in., Diameter: 2.38 in., Base Type: E26 (medium screw base), Life Hours: 2,500, Features: Frosted Glass

Detailed Specifications

Voltage	34V
Wattage	100W
Type	A19 Light Bulb
Length	4.10 in.
Diameter	2.38 in.
Base Type	E26 (medium screw base)
Average Life Hours	2500
Color Emitted	Frosted Glass
Is It Dimmable?	Yes

There are no reviews for this product.

Write a review

* Your Name

* Your Review

* Star Rating Fair 1 2 3 4 5 Excellent

100A19/34V