

Detailed Specifications

[SSL Secure Online Payment Processing](#)



- [Description](#)
- [Specification](#)
- [Reviews \(0\)](#)

Voltage: 120V, Wattage: 250W, Brand: Norman Lamps, Life Hours: 6,000, Base Type: E26 (medium screw base), Lamp Shape: Reflector, Type: BR40 Infrared Heat Reflector Bulb, Case Quantity: Order 12 for a full case, Color Emitted: Clear Glass, Dimmable: Yes, Features: High temperature (PFA) Tuff-Coat shatter resistant coating applied.

Detailed Specifications

Voltage	120V
Wattage	250W
Type	BR40 Reflector Bulb
Lamp Shape	Reflector
Diameter	5 in.
Base Type	E26 (medium screw base)
Average Life Hours	6,000
Case Quantity	Order 12 for a full case
Color Emitted	Clear Glass
Is It Dimmable?	Yes
Features	Tuff-Coat Shatter Resistant

There are no reviews for this product.

## Write a review

\* Your Name

\* Your Review

\* Star Rating Fair  1  2  3  4  5 Excellent

