

Watts	Amps	Ohms	Sq. Ft.	Length (ft)	Model No.	Number of cable guides**
170	0.7	338	15	54	N2C015	12
242	1.0	238	20	73	N2C020	24
313	1.3	184	25	98	N2C025	24
420	1.8	137	35	131	N2C035	36
546	2.3	105	45	169	N2C045	36
637	2.7	90	55	205	N2C055	36
767	3.2	75	65	240	N2C065	48
864	3.6	67	70	272	N2C070	60
1032	4.3	56	85	334	N2C085	60
1110	4.6	52	90	356	N2C090	60
1218	5.1	47	100	393	N2C100	60
1446	6.0	40	120	461	N2C120	84
1632	6.8	35	135	525	N2C135	96
1726	7.2	33	145	551	N2C145	108
1920	8.0	30	160	620	N2C160	108
2040	8.5	28	170	665	N2C170	120
2316	9.7	25	190	750	N2C190	120
2604	10.9	22	215	839	N2C215	132
2934	12.2	20	240	953	N2C240	144