

High Speed HDMI with Ethernet CL3 Cables | Features Guide

Part #	Length	High Speed w/ Ethernet	1080p (120hz) Max Refresh Rate at 10.2 Gps	4K (Ultra HD)	Dolby TrueHD Audio	3D Support	DTS-HD Master Audio	32 Bit Deep Color	Fire Rated UL/CL3	HDMI Ethernet Channel	Auto Return Channel (ARC)	Gold plated Individually Sealed Conductors
AC2M00-BK	0.7m (2.3')	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
AC2M01-BK	1m (3.3')	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
AC2M02-BK	2m (6.6')	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
AC2M03-BK	3m (9.8')	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
AC2M04-BK	4m (13.1')	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
AC2M05-BK	5m (16.4')	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
AC2M07-BK	7.5m (24.6')	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
AC2M10-BK	10m (32.8')	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
AC2M15-BK	15m (49.2')	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
AC2M20-BK	20m (65.6')	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓



The professional choice for HDMI cables and accessories

This comprehensive line of pro-grade HDMI products — which includes CL3-rated High-Speed cables, couplers, repeaters and extenders — delivers an unparalleled HD audio and video experience.

- Provides uncompressed HD video and 8-channel digital audio in a single cable
- Supports 3D, 1080p, 4K (Ultra HD) & 32 Bit Deep Color video
- Supports Dolby TrueHD and DTS-HD Master Audio
- Audio Return Channel (ARC) and HDMI Ethernet Channel (HEC) capable
- All cable lengths CL3-rated for in-wall use
- Compatible with HDTVs, DVD/Blu-ray players, cable & satellite set top boxes, and gaming consoles
- Gold-plated connectors with individually shielded conductors ensure maximum resolution

