

8x8 Enhanced Combo Module, Security

364400-13



The enhanced combo modules include the features of the Basic Combination Modules while providing maximum flexibility for system reconfiguration and performance testing of cable runs. Supports telecom distribution to outlets via RJ45 modular jack connections. 5 1/8"H x 6 1/2"W

features & benefits

Security models support Security System Interface for telephone line seizure
RJ45 modular plug connections allow easy reconfiguration of services between telephone and data

specifications

General Info

Color: Black
finish: Powder Coat
Type: Telecom/Video Module

Assembly/Installation Information

Mounting Hardware Included: Yes

Listing Agencies/Third Party Information

U N SPS C: 43222819

Construction Information

Installation Location: Enclosure

Dimensions

Height Metric: 13 cm

Height U S: 5.125 in

Length U S: 3.28 in

Length Metric: 8.3 cm

Width Metric: 16.5 cm

Width U S: 6.5 in

Cord Information

Max Insertion Loss: 5-40MHz: 10dB, 40-600MHz: 11dB, 600-1000MHz: 12dB

Max Return Loss: Minimum: 5-40MHz: 9dB, 400-600MHz: 15dB, 600-1000MHz: 12dB

Technical Information

Bracket Required: Mounting plate 100356-01 included

Frequency: 5-1000 MHz

Humidity: 90% Relative Humidity (Non-Condensing)

Material: 18 Gauge CRS

Mounting: Mount directly in any On-Q style enclosure

Operating Temperature Celsius: 0°C to 50°C

Operating Temperature Fahrenheit: 32°F to 122°F

Output Impedance: 75 ohms

Product Fits Into: On-Q Style Enclosure

Shape: Rectangular

Receptacle Type: 8x RJ45 Telecom, 8x RG6 "F", 1x RJ31x

Number Of Receptacles: 17