



Actual

**Catalog Number:** ADR02-34  
**Product ID:** 7TAH006600R0192  
**UPC Number:** 78378661003  
**Status:** Active

Type ADR-ALCUL Three-Conductor, Four-Hole Mount for Conductor Range Max 2 Str., Min 14 AWG

- Easy Installation - no special tools required.

#### North American Specifications (UNSPSC)

|                                |  |
|--------------------------------|--|
| UNSPSC                         | 39121408 Mechanical connectors                 |
| IGCC                           | 4541 Mechanical connectors                     |
| Brand Name                     | Blackburn                                      |
| Type                           | Dual-Rated Mechanical Connector                |
| Special Features               | Easy Installation - no special tools required. |
| Standard                       | UL E9809                                       |
| Number Of Conductors           | 3  |
| Material                       | Aluminum                                       |
| Finish                         | Tin-Plated                                     |
| Conductor Range (Main/Primary) | 14-2 AWG                                       |
| Number Of Mounting Holes       | 4  |

#### Packaging

|                           |                  |
|---------------------------|------------------|
| Outer Quantity            | 6                |
| Outer Dimensions (inches) | 700x500x0        |
| Weight Uom                | 8.5 lbs. per 100 |

#### Documents / Support Tools

|                         |                      |
|-------------------------|----------------------|
| Technical Data Sheet CA | Available on Website |
|-------------------------|----------------------|

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com