



Actual



Family

Catalog Number: AMTS25064
Product ID: 7TAH006400R0139
UPC Number: 78378666969
Status: Active

AMT 4 Port Same Side PVC Connector, Ultraviolet Resistant, Wire Range 250 kcmil-6 Str, Length 4.06 Inches, Width 2.13 Inches, Height 2.13 Inches, Hex Size 5/16 Inch

- PVC Insulation eliminates insulation failures and reduces outage costs. Removable port and screw plugs.
- Compact design provides space efficiencies.
- All cable entry are equipped with an anti-oxidation compound.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	AMT Connector
Special Features	PVC Insulation eliminates insulation failures and reduces outage costs. Removable port and screw plugs.
Standard	UL E9809
Material	Aluminum
Color	Black
Voltage Rating	600V
Insulation	PVC
Number Of Ports	4

Packaging

Outer Quantity	6
Outer Dimensions (inches)	1.91x2.17x2.17
Weight Uom	47.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Marketing Brochure US 1	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com