

FIRE ALARM CABLE

**Power Limited-Type FPLP - Plenum Rated
Nonshielded - 300 Volt**



Conductor:

- Solid bare copper

Insulation:

- Color coded Omniplen

Assembly:

- Conductors cabled together

Jacket:

- Red PVC

Applications:

- Fire alarm systems
- Smoke detectors
- Burglar alarms
- Dedicated Fire Protective Circuits

Standards:

- UL Listed Type FPLP
- NEC Article 760

Part #	AWG Size	No. of Cond.	Nom. Insul. Thick.	Nom. Jacket Thick	Nom. O.D.	Lbs./M?	West Penn
H21802	18	2	.006"	.016"	.136"	18	60980B
H21804	18	4	.006"	.016"	.158"	28	60982B
H21806	18	6	.006"	.016"	.196"	43	-
H21808	18	8	.006"	.020"	.212"	58	-
H21602	16	2	.008"	.020"	.174"	26	60991B
H21604	16	4	.008"	.020"	.202"	45	60164B
H21402	14	2	.009"	.020"	.204"	38	60993B
H21404	14	4	.009"	.020"	.238"	70	60700B
H21202	12	2	.008"	.021"	.236"	57	60995B

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.

Color Code Chart 112:

Cond. Num.	Color	Cond. Num.	Color
1	Black	2	Red
3	Brown	4	Blue
5	Yellow	6	Orange
7	Green	8	White