

TVI MOTORIZED LENS BULLET

LTBC2812IR-MZ



Features

- 2.2 Megapixel HD-TVI Bullet
- HD 1080p Resolution
- Motorized Zoom and Focus
- Varifocal 2.8-12mm Lens
- True Wide Dynamic Range 120dB
- 120ft IR Range
- Matrix IR LED
- Smart IR Technology
- Outdoor Rated IP66
- Digital Noise Reduction
- Up the Coax Control
- Dual Volt - DC 12V & AC 24V

Model Number	LTBC2812IR-MZ
Resolution	2 Megapixel 1080p
Effective Pixels	1928(H)*1088(V)
Image Sensor	CMOS Sensor
Signal System	NTSC/PAL
Min. Illumination	0.01 Lux @ (F1.2,AGC ON),0 Lux with IR
Shutter speed	1/25 s to 1/50,000 s
Lens	2.8-12mm @ F1.2, Angle of view: 92° - 32°
Lens Adjustment	Motorized Zoom/Focus from joystick or recorder PTZ menu
Lens Mount	φ14
Day & Night	True Day Night IR Cut Filter
IR Range	Up to 120 ft
Wide dynamic range	120dB True WDR
Synchronization	Internal synchronization
Video Frame Rate	1080p@30fps
Video Output	1 BNC Analog HD-TVI output
Scene	Adjustable - Indoor, Outdoor, Indoor1, LOW-LIGHT
Camera ID	On/off (15 characters, position programmable)
AGC	Support
D/N Mode	Color/BW/EXT
White Balance	ATW, AWC-SET, Indoor, Outdoor, Manua
Privacy Mask	On/Off, maximum 2 zones
Motion Detection	On/Off, maximum 4 zones
BLC	Support
Anti-flicker	On/off
Language	English, Japanese, CHN1, CHN2, Korean, German, French, Italian, Spanish, Russian,
Function	Eclipse, DNR, Digital zoom(62x), Slow shutter, Mirror, Defog, Defect pixel
Working Temperature	-40 °C - 60 °C (-40 °F - 140 °F)
Humidity	Humidity 90% or less (non-condensing)
Power Supply	Dual Volt - DC12V / AC24V
Power Consumption	12VDC: Max. 7W ; 24VAC: Max. 10W
Weather Proof Ratings	IP66
Communication	Up the coax control, Zoom/Focus & OSD control
Dimensions	3.62" x 3.34" x 3.34"
Weight	1.98 lbs