



LCDI-4T

4" Video Test Monitor



-Features-

- Straps on to arm
- Leather Case
- Rechargeable
- Wide View Angle
- TFT LCD

-Specifications-

LCDI-4T	
LCD Size	4" LCD Panel
Resolution	480 x 234
Brightness	250cd/m2
Contrast Ratio	150:1
View Angle	10°/30°/45°/45°
System	NTSC
Video Input	1.0 Vp-p @ 75Ω
Audio Input	30mVp-p ~ 100m Vp-p
Video Connector	I/O BNC
Audio Connector	I/O RCA
User Controls	OSD Control (Digital Control, Power On/Off, Contrast, Brightness, Color, Tint, Volume)
Battery	Ni0MH Rechargeable; Battery x 6 size "AA"
Case	Leather
Power	12V DC
Power Consumption	3.2 W Max
Dimensions	6" x 4.2" x 1.5"
Weight	0.7 lb
Operating Temp	14° ~ 122° F (-10° ~ 50° C)