

OPTICOM**LCDI-15A, LCDI-17A, LCDI-19A**
15", 17", 19" CCTV Monitor**Features**

VESA Standard Mounting Pattern

LED Back Light

Picture in Picture

Remote Control Included

More Features

3D De-interlace

3D Comb Filter

OSD

DC 12V Power Supply
Included

Audion In/Out

Stand Included

Specification	LCDI-15A	LCDI-17A	LCDI-19A
LCD Panel	15"	17"	19"
Viewable Area	304 x 228	337.9 x 270.3	376 x 301
Profile Ratio	4:3	5:4	
Max. Resolution	1024 x 768	1280 x 270.3	1280 x 1024
Display Colors	16.7M		
Brightness	250 cd/m ²		
Contrast	600:1	1000:1	
Response Time	6/2 ms	3.8/1.2 ms	1.3/3.7 ms
Video Input	1 x BNC In/Out, 1 x VGA, 2 x HDMI, 1 x USB		
View Angle (U/D/L/R)	80/80/80/80	80/80/85/85	75/85/85/85
Housing	High Impact Plastic		
Dimensions	14.1 x 11.2 x 2.6"	15.4 x 13.9 x 2.6"	17 x 14.1 x 2.7"
Weight	7.1 lbs	8.6 lbs	10.6lbs
Operating Temperature	32° ~ 104° F (0° ~ 40° C)		