

NVD-121

Outdoor Vandal Dome Camera



-Features-

- High Resolution
- IP-68 Rated
- 2DDNR
- Privacy Mask
- Easy Twist and Lock Installation



NVD-121

Sensor	1/3" Sony Super HAD CCD
Resolution	620 TV Lines
Lens	2.8-12mm
Scanning System	2:1 Interlaced
Illumination	0.1 Lux Color / 0.01 Lux B&W
S/N Ratio	More than 50dB
Video Output	1.0 Vp-p Comp. 75 Ohms
White Balance	ATW1 / AWC2 / AWC ->2 SET / Manual Adjustable
Electronic Shutter	Auto (1/60sec ~ 1/100,000sec)
OSD	Built-in
Backlight Compensation	Low / BLC / HLC
Auto Gain Control	Low / Middle / High / Off
2D DNR	On / Off
Day & Night	Auto / Color / BW / EXT
Privacy	On / Off (8 zone)
Motion Detection	On / Off
Image Conversion	On / Off
Sharpness	Adjustable
Dimensions	5.5" (Ø) x 4.0" (H)
Weight	2.5 lbs
Power	DC 12V or AC 24V
Operating Temp	14° ~ 122°F (-10° ~ 50°C)