

NVD-183

Outdoor Vandal Dome Camera



-Features-

- High Resolution
- Sens-up
- IP-68 Rated
- 3DDNR
- SS-WDR
- Privacy Mask
- Easy Twist and Lock Installation

	OSD	DNR	WDR	DIS	LSC	HLM				
	On Screen Display	Digital Noise Reduction	Wide Dynamic Range	Digital Image Stabilizer	Lens Shading Compensation	High Light Mask	Motion Detection	WATER PROOF IP-68	Tri-Axis	Dual Power AC/DC

Digital Zoom	Vandal Proof

NVD-183	
Sensor	1/3" Sony Super HAD CCD
Resolution	650 TV Lines
Lens	2.8-12mm
Scanning System	2:1 Interlaced
Illumination	0.3 Lux Color / 0.002Lux B&W
S/N Ratio	More than 50dB
Video Output	1.0 Vp-p Comp. 75 Ohms
White Balance	ATW / AWC / PUSH / Manual
Electronic Shutter	Auto / Manual (1/60sec ~ 1/100,000sec)
WDR	Auto / Off
OSD	Built-in
Backlight Compensation	Low / Middle / High / HLM / Off
Auto Gain Control	Low / Middle / High / Off
3D DNR	Low / Middle / High / Off
Day & Night	Auto / Color / BW / CDS
Privacy	On / Off (6 zone)
Motion Detection	On / Off (240 zone)
Image Conversion	Freeze / V-Flip / H-Flip / Rotate / Nega: All On / Off Adjustable
DIS	On / Off
LSC	On / Off
Digital Zoom	On (x1 ~ 10) / Off
Sharpness	Adjustable
Dimensions	5.5"(Ø) x 4.0"(H)
Weight	2.5 lbs
Power	DC 12V
Operating Temp	14° ~ 104°F (-10° ~ 40°C)