

SVC-100

High Resolution Indoor Dome Camera



-Features-

- High Resolution
- Day/Night
- Easy Flip Open Case



SVC-100

Sensor	1/3" Color
Resolution	470 TV Lines
Lens	3.6mm
Scanning System	2:1 Interlaced
Illumination	0.3 Lux
S/N Ratio	50dB
Gamma	r=0.45
Video Output	1.0 Vp-p Comp. 75 Ohms
Electronic Shutter	1/60sec ~ 1/100,000
Day / Night	Auto / On
Backlight	Built-in
Compensation	
Auto Gain Control	Built-in
White Balance	AWB
Dimensions	5.0"(Ø) x 3.5"(H)
Weight	1.1 lbs
Power	DC 12V, 120mA
Operating Temp	14° ~ 122°F (-10° ~ 50°C)