

OPTICOM**PXD-3400****Prime Series Hybrid DVR (4/8/16 Channel)**

Features

H.264 High Profile Compression

HD-TVI/HD-AHD/Analog

HDMI & VGA Outputs

More Features

Mobile App

“AVY Viewers HD”

- iPad
- iPhone
- Android

POS Integration

Specification	PXD-3404	PXD-3408	PXD-3416
OPERATING SYSTEM	EMBEDDED LINUX		
OS FIRMWARE	LINUX OS IN FLASH MEMORY		
MEMORY	512 MB DOR3 MEMORY	1GB DOR3 MEMORY	2GB DOR3 MEMORY
VIDEO INPUT	4 BNC	8 BNC	16 BNC
RECORDING RATE (MAX.)	720P:480/400FPS(NTSC/PAL),1080P:240/200FPS(NTSC/PAL)		
AUDIO INPUT / OUTPUT	4/1	8/1	16/1
ALARM INPUT / OUTPUT	4/1 (RELAY)	8/1 (RELAY)	16/1 (RELAY)
ETHERNET	10M / 100M ETHERNET		RJ45 10M / 100M / 1000M ETHERNET
USB 2.0	2xUSB (1xFRONT PANEL, 1x REAR PANEL)		
USER INTERFACE (GUI)	KEYPAD,MOUSE,PTZ CONTROL, REMOTE CONTROLLER		
ARCHIVE FILE FORMAT	EXE (VIDEO CLIP) / AM (VIDEO CLIP) /JPEG (STILL IMAGE)		
NTP SERVER	YES		
GMT TIME ZONE	YES		
AUTO DST	YES		
RECORDING QUALITIES	SUPER / HIGH / STANDARD / LOW		
RECORDING MODES	CONTINUOUS / ALARM / MOTION / EMERGENCY		
MOTION DETECTION	YES (30 x 20)		
PLAYBACK CONTROL	X1,x2,x6,x8,x16,x32,x64, EXTREME		
PTZ CONTROL	RS-485/422 (TERMINAL BLOCK),UTC OVER BNC (CONTROL OVER COAX)		
TEXT INSERTION (POS)	4		
CENTRAL MONITORING	CMS PRO (WINDOWS) / ICMS (MAC) / WEB CLIENT PRO		
MOBILE VIEWER	AVY Viewers HD (PAD) / IPHONE / ANDROID		
PRIMARY STORAGE	1x SATA HDD (UP TO 6TB)		2x SATA HDD (UP TO 12TB)
CLIP COPY STORAGE	USB MEMORY STICK / OVER THE NETWORK		
DIMENSION (WxHxD)	295mm x 45mm x 210mm		370mm x 45mm x 315mm
OPERATING TEMPERATURE	5 C~40 C /41'F-104'F		
OPERATING HUMIDITY	0% - 90%		
POWER SUPPLY	DC 12V,2A		DC 12V,5A
CONSUMPTION	<9W (WITHOUT HDD)		<30W (WITHOUT HDD)

Opticom Tech
www.opticomtech.com
www.toughestvideocamera.com

Sales Office: 800-578-1853
 Sales Fax: 888-370-5656
 Sales E-mail: Info@OpticomTech.com