



DULUX® EL SELF-BALLASTED COMPACT FLUORESCENT LAMPS

Decorative Compact Fluorescent Lamps

Nominal Wattage	Bulb	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Avg Rated Life (hrs)	CCT (K)	CRI	Approx Lumens Initial @25°C/77°F	Approx Lumens Mean	Symbols & Footnotes
5	FLAME	5.06	Medium	29742	CF5EL/B10/DIM/830	120	6	25000	3000	82	200	160	1,3,8, 9,12,14,20
7	FLAME	5.0	Medium	29039	CF7EL/B15/827	120	6	6000	2700	82	280	224	1,3,8, 9,12,14,20
				29167	CF7EL/B15/830/BL	120	6	6000	3000	82	280	224	1,3,8, 9,12,14,20
9	FLAME	4.25	Candelabra	29584	CF9EL/B14/C/830/ADP/BL2	120	12	8000	3000	82	450	360	1,3,8, 9,12,14,20

Globe Compact Fluorescent Lamps

Nominal Wattage	Bulb	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Avg Rated Life (hrs)	CCT (K)	CRI	Approx Lumens Initial @25°C/77°F	Approx Lumens Mean	Symbols & Footnotes
9	G25	4.25	Medium	29414	CF9EL/G25/827	120	6	8000	2700	82	495	396	1,3,8, 9,12,14,20
				29528	CF9EL/G25/830/BL2	120	12	8000	3000	82	495	396	1,3,8, 9,12,14,20
14	G30	5.5	Medium	29195	CF14EL/G30/830	120	6	6000	3000	82	700	560	1,3,8, 9,12,14,20

Reflector Compact Fluorescent Lamps

Nominal Wattage	Bulb	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Avg Rated Life (hrs)	CCT (K)	CRI	Approx Lumens Initial @25°C/77°F	Approx Lumens Mean	Symbols & Footnotes
9	R20	3.94	Medium	29638	CF9EL/R20/827	120	6	8000	2700	82	300	240	1,3,8, 9,12,14,20
				29640	CF9EL/R20/830/BL	120	6	8000	3000	82	300	240	1,3,8, 9,12,14,20
14	R20	4.25	Medium	29624	CF14EL/R20/827	120	6	8000	2700	82	495	396	1,3,8, 9,12,14,20
				29587	CF14EL/R20/830/BL	120	6	8000	3000	82	495	396	1,3,8, 9,12,14,20
15	BR30	5.5	Medium	29465	CF15EL/BR30/DIM/827	120	6	6000	2700	82	600	480	1,3,8, 9,12,14,20
				29667	CF15EL/BR30/DIM/830/BL	120	6	8000	3000	82	600	480	1,3,8, 9,12,14,20
		5.6	Medium	29539	CF15EL/BR30/850/BL	120	6	6000	5000	82	560	448	1,3,8, 9,12,14,20
16	BR30	5.7	Medium	29591	CF16EL/BR30/827	120	6	8000	2700	82	750	600	1,3,8, 9,12,14,20
				29590	CF16EL/BR30/830	120	6	8000	3000	82	750	600	1,3,8, 9,12,14,20
19	PAR38	5.8	Medium	29581	CF19EL/PAR38/830	120	6	8000	3000	82	950	760	1,3,8, 9,12,14,20
20	BR40	6.5	Medium	29399	CF20EL/BR40/827	120	6	8000	2700	82	900	720	1,3,8, 9,12,14,20
				29363	CF20EL/BR40/830	120	6	8000	3000	82	900	720	1,3,8, 9,12,14,20
23	PAR38	6.25	Medium	29359	CF23EL/PAR38/827	120	6	8000	2700	82	1200	960	1,3,8, 9,12,14,20