

## OCTRON® AND OCTRON® CURVALUME® FLUORESCENT LAMPS

### OCTRON® 800 XP® 4 Foot SUPERSAVER® Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start (@12hrs/start)	CCT (K)	CRI	Approx Lumens Initial @25°C/77°F	Approx Lumens Mean @25°C/77°F	Symbols & Footnotes
30	T8	48	47.78	Med Bipin	22063	F030/830/XP/SS/ECO	30	36000 (42000)	3000	85	2850	2710	31,33,44,48,52,76,94,95
					22060	F030/835/XP/SS/ECO	30	36000 (42000)	3500	85	2850	2710	31,33,44,48,52,76,94,95
					22062	F030/841/XP/SS/ECO	30	36000 (42000)	4100	85	2850	2710	31,33,44,48,52,76,87,95
					22202	F030/850/XP/SS/ECO	30	36000 (42000)	5000	85	2800	2660	31,33,44,48,52,76,94,95

### OCTRON® 800 XP® Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start (@12hrs/start)	CCT (K)	CRI	Approx Lumens Initial @25°C/77°F	Approx Lumens Mean @25°C/77°F	Symbols & Footnotes
32	T8	48	47.78	Med Bipin	22039	F032/827/XP/ECO	30	36000 (42000)	2700	85	3000	2850	20,31,33,48,52,76,94
					21759	F032/830/XP/ECO	30	36000 (42000)	3000	85	3000	2850	20,31,33,48,52,76,94
					21763	F032/835/XP/ECO	30	36000 (42000)	3500	85	3000	2850	20,31,33,48,52,76,94
					21767	F032/841/XP/ECO	30	36000 (42000)	4100	85	3000	2850	20,31,33,48,52,76,94
					22026	F032/850/XP/ECO	30	36000 (42000)	5000	85	3000	2850	20,31,33,48,52,76,94
					21720	F032/865/XP/ECO	30	36000 (42000)	6500	85	2850	2708	20,31,33,48,52,76,94
					22594	F032/SKYWHITE/XP/ECO	30	36000 (42000)	8000	88	2650	2518	20,31,33,48,52,76,94

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	CRI	Approx Lumens Initial @25°C/77°F	Approx Lumens Mean @25°C/77°F	Symbols & Footnotes
17	T8	24	23.78	Med Bipin	21587	F017/827/XP/ECO	30	24000	2700	85	1375	1305	31,33,44,48,52,76,87
					21785	F017/830/XP/ECO	30	24000	3000	85	1375	1305	31,33,44,48,52,76,87
					21778	F017/835/XP/ECO	30	24000	3500	85	1375	1305	31,33,44,48,52,76,87
					21907	F017/841/XP/ECO	30	24000	4100	85	1375	1305	31,33,44,48,52,76,87
					22193	F017/850/XP/ECO	30	24000	5000	85	1375	1305	31,33,44,48,52,76,87
					21718	F017/865/XP/ECO	30	24000	6500	85	1250	1188	31,33,44,48,52,76,87
25	T8	36	35.78	Med Bipin	21586	F025/827/XP/ECO	30	24000	2700	85	2175	2065	31,33,44,48,52,76,87
					21910	F025/830/XP/ECO	30	24000	3000	85	2175	2065	31,33,44,48,52,76,87
					21776	F025/835/XP/ECO	30	24000	3500	85	2175	2065	31,33,44,48,52,76,87
					21774	F025/841/XP/ECO	30	24000	4100	85	2175	2065	31,33,44,48,52,76,87