





DULUX[®] EL

When considering your lighting options, Energy Savings, Long Life/Maintenance Cost Savings and Color Excellence are key factors. SYLVANIA products can help you make the right decision.

Compact Fluorescent Lamps



	Item Number	Ordering Abbreviation	Replaced Incandescent Wattage	Nominal Wattage	Initial Lumens	Color Temp.	CRI	Average Rated Life (hrs.)	
Micro-Mini Twist 	21095	CF5EL/MICRO/827/LS/RP†	25	5	250	2700K	82	12,000	
	29160	CF5EL/MICRO/827/RP	25	5	300	2700K	82	12,000	
	26944	CF10EL/MICRO/827/RP3 18/CS 3/SKU	40	10	600	2700K	82	10,000	✓
	29401	CF10EL/MICRO/827	40	10	600	2700K	82	12,000	✓
	26929	CF13EL/MICRO/865/RP3 18/CS 3/SKU	60	13	800	6500K	82	10,000	
	26943	CF13EL/MICRO/827/RP3	60	13	825	2700K	82	10,000	✓
	26927	CF13EL/MICRO/835/RP3 18/CS 3/SKU	60	13	825	3500K	82	10,000	✓
	29972	CF13EL/MICRO/827/LS/RP2†	60	13	800	2700K	82	12,000	✓
	26938	CF13EL/MICRO/C/827/LS/BL2†	60	13	800	2700K	82	12,000	✓
	26936	CF13EL/MICRO/C/865/BL2	60	13	800	6500K	82	12,000	
	29727	CF13EL/MICRO/827/RP2	60	13	825	2700K	82	12,000	✓
	29898	CF13EL/MICRO/830/ECO	60	13	825	3000K	82	12,000	
	26932	CF13EL/MICRO/C/835/BL2	60	13	825	3500K	82	12,000	✓
	26941	CF13EL/MICRO/C/827/BL2	60	13	825	2700K	82	12,000	✓
	26942	CF13EL/MICRO/827/15000HR/RP2	60	13	825	2700K	82	15,000	
	26925	CF20EL/MICRO/827/RP3 18/CS 3/SKU	75	20	1300	2700K	82	10,000	✓
	29973	CF20EL/MICRO/827/LS/RP2†	75	20	1200	2700K	82	12,000	
	29728	CF20EL/MICRO/827/RP2	75	20	1300	2700K	82	12,000	✓
	29899	CF20EL/MICRO/830/ECO	75	20	1300	3000K	82	12,000	
	26924	CF20EL/MICRO/827/15000HR RP2	75	20	1300	2700K	82	15,000	
	28975	CF23EL/MICRO/865/RP3 18/CS 3/SKU	100	23	1450	6500K	82	10,000	
	28976	CF23EL/MICRO/827/RP3 18/CS 3/SKU	100	23	1600	2700K	82	10,000	✓
	26928	CF23EL/MICRO/835/RP3 18/CS 3/SKU	100	23	1630	3500K	82	10,000	✓
	29974	CF23EL/MICRO/827/LS/RP2†	100	23	1400	2700K	82	12,000	
	28952	CF23EL/MICROLED/827/HVP	100	23	1600	2700K	82	12,000	
	29729	CF23EL/MICRO/827/RP2	100	23	1640	2700K	82	12,000	✓
	29901	CF23EL/MICRO/830/ECO	100	23	1640	3000K	82	12,000	
	26906	CF23EL/MICRO/C/827/BL2	100	23	1640	2700K	82	12,000	✓
	26939	CF23EL/MICRO/827/15000HR RP2	100	23	1640	2700K	82	15,000	
	29023	CF26EL/MICRO/827/LS†	100	26	1600	2700K	82	12,000	
29026	CF26EL/MICRO/827 6/CS	100	26	1750	2700K	82	12,000		
28990	CF26EL/MICRO/830/ECO	100	26	1750	3000K	82	12,000		
Super Mini Twist 	29707	CF7EL/SUPER/827/RP	25	7	375	2700K	82	10,000	
	29708	CF11EL/SUPER/827/RP	40	11	600	2700K	82	10,000	✓
	29041	CF13EL/SUPER/827/RP3	60	13	875	2700K	82	8,000	✓
	29782	CF13EL/SUPER/850/RP	60	13	800	5000K	82	10,000	
	29711	CF13EL/SUPER/865/RP	60	13	800	6500K	82	10,000	
	29722	CF13EL/SUPER/865/RP3	60	13	800	6500K	82	10,000	
	29710	CF13EL/SUPER/827/RP	60	13	875	2700K	82	10,000	✓
	29693	CF19EL/SUPER/827/RP	75	19	1250	2700K	82	10,000	✓
	29726	CF19EL/SUPER/827/RP	75	19	1250	2700K	82	10,000	
	29674	CF23EL/SUPER/865/RP	100	23	1500	6500K	82	10,000	
	29721	CF23EL/SUPER/865/RP3	100	23	1500	6500K	82	10,000	
	29712	CF23EL/SUPER/827/RP	100	23	1600	2700K	82	10,000	✓
	29694	CF23EL/SUPER/827/RP3	100	23	1600	2700K	82	10,000	✓
	29699	CF23EL/SUPER/850/RP	100	23	1600	5000K	82	10,000	
	Mini Twist 	29379	CF7EL/MINI/830	25	7	375	3000K	82	8,000
29378		CF11EL/MINI/830	40	11	600	3000K	82	8,000	✓
29376		CF13EL/MINI/830	60	13	875	3000K	82	8,000	✓
29781		CF13EL/MINI/835/DAY/RP	60	13	875	3500K	82	8,000	✓
29567		CF13EL/MINI/841	60	13	800	4100K	82	10,000	
29149		CF13EL/MINI/827/CVP 12/CS	60	13	875	2700K	82	10,000	✓
29120		CF13EL/MINI/827/CVP 6/CS	60	13	875	2700K	82	10,000	✓
29780		CF13EL/MINI/835/DAY/RP3	60	13	875	3500K	82	10,000	✓
29396		CF19EL/MINI/830	75	19	1200	3000K	82	8,000	
29614		CF23EL/MINI/827/CVP	100	23	1600	2700K	82	8,000	✓
29397		CF23EL/MINI/830	100	23	1600	3000K	82	8,000	✓
29784		CF23EL/MINI/835/DAY/RP	100	23	1600	3500K	82	8,000	✓
29411		CF23EL/MINI/827	100	23	1600	2700K	82	10,000	✓
29564		CF23EL/MINI/841	100	23	1600	4100K	82	10,000	
Twist 		28957	CF13EL/GU24/827/BL	60	13	800	2700K	82	8,000
	29454	CF14EL/TWIST/827/DIM/BL	60	14	800	2700K	82	8,000	✓
	28946	CF23EL/TWIST/827/DIMBASE 4/CS 1/SKU	100	23	1500	2700K	82	8,000	
	29947	CF23EL/GU24/827/BL	100	23	1600	2700K	82	8,000	
	29453	CF24EL/TWIST/827/DIM/BL	100	24	1500	2700K	82	8,000	
	29793	CF30EL/TWIST/835/DAY/RP	125	30	1845	3500K	82	10,000	✓
	29395	CF30EL/TWIST/827	125	30	2000	2700K	82	10,000	✓
	29792	CF30EL/TWIST/827/RP	125	30	2000	2700K	82	10,000	✓
29786	CF40EL/TWIST/827/RP	150	40	2600	2700K	82	10,000	✓	
29508	CF65EL/TWIST/841	200	65	4200	4100K	82	8,000		

General Purpose