











DULUX® EL

Compact Fluorescent Lamps

	Item Number	Ordering Abbreviation	Replaced Incandescent Wattage	Nominal Wattage	Initial Lumens	Color Temp.	CRI	Average Rated Life (hrs.)		
General Purpose	3-Way Twist 	26933	CF33EL/3WAY/865/BL	30	12	540	6500K	82	10,000	
				70	22	1080	6500K	82	10,000	
				100	33	1935	6500K	82	10,000	
		29747	CF33EL/3WAY/827	50	12	600	2700K	82	10,000	✓
				100	22	1200	2700K	82	10,000	✓
				150	33	2150	2700K	82	10,000	✓
		26930	CF33EL/3WAY/835/BL	50	12	600	3500K	82	10,000	
				100	22	1200	3500K	82	10,000	
				150	33	2150	3500K	82	10,000	
		29913	CF33EL/3WAY/830/RP	50	12	600	3000K	82	10,000	✓
				100	22	1200	3000K	82	10,000	✓
				150	33	2150	3000K	82	10,000	✓
		28974	CF33EL/3WAY/827/LS/RP†	50	12	600	2700K	82	10,000	✓
				100	22	1200	2700K	82	10,000	✓
				150	33	1750	2700K	82	10,000	✓
		27714	CF40EL/3WAY/827/RP	60	20	1000	2700K	82	8,000	✓
				120	30	2050	2700K	82	8,000	✓
				150	40	2650	2700K	82	8,000	✓
	29196	CF14EL/B/830	60	14	700	3000K	82	6,000	✓	
Classic A-line 	28962	CF5EL/A15/DIM/827/BL	15	5	200	2700K	82	25,000	✓	
	28963	CF9EL/A15/DIM/827/BL2	40	9	450	2700K	82	8,000	✓	
	29791	CF9EL/A15/DIM/827/BL2	40	9	450	2700K	82	8,000	✓	
	29468	CF14EL/A19/830	60	14	800	3000K	82	6,000	✓	
	29680	CF14EL/A19/827/RP	60	14	800	2700K	82	8,000	✓	
										✓
Decorative	G25 	29474	CF9EL/G25/827/BL	40	9	495	2700K	82	8,000	✓
		29414	CF9EL/G25/827	40	9	500	2700K	82	8,000	✓
	B10 	29195	CF14EL/G30/830	60	14	700	3000K	82	6,000	✓
		29121	CF4EL/B10/C/830/BL	15	4	170	3000K	82	6,000	✓
		28964**	CF5EL/B10/C/DIM/827/BL*	15	5	200	2700K	82	25,000	✓
		29750**	CF5EL/B10/C/DIM/827/BL*	15	5	200	2700K	82	25,000	✓
		28932**	CF5EL/B10/DIM/827/BL*	15	5	200	2700K	82	25,000	✓
		29742**	CF5EL/B10/C/DIM/827/BL*	15	5	200	2700K	82	25,000	✓
		28941	CF9EL/B10/827/BL2	40	9	450	2700K	82	8,000	✓
		25986	CF9EL/B10/C/827/BL2	40	9	450	2700K	82	8,000	✓
29600	CF9EL/B10/C/830	40	9	450	3000K	82	8,000	✓		
Specialty	Bug 	29789	CF14EL/A19/YELLOW/RP	—	14	—	—	—	6,000	✓
Directional	R20 	29638	CF9EL/R20/827	40	9	300	2700K	82	8,000	✓
		29760	CF14EL/R20/827	50	14	500	2700K	82	8,000	✓
		29562	CF14EL/R20/827/BL	50	14	500	2700K	82	8,000	✓
		29634	CF14EL/R20/830	50	14	500	3000K	82	8,000	✓
		28998	CF14EL/R20/DIM/827/RP*	50	14	500	2700K	82	8,000	✓
	BR30 	29496	CF15EL/BR30/DIM/827/RP*	65	15	700	2700K	82	6,000	✓
		28954	CF15EL/BR30/DIM/827/BL	65	15	700	2700K	82	8,000	✓
		26937	CF16EL/BR30/LS/827/BL†	65	16	650	2700K	82	8,000	✓
		26934	CF16EL/BR30/865/RP	65	16	700	6500K	82	8,000	✓
		29565	CF16EL/BR30/827/BL	65	16	750	2700K	82	8,000	✓
		29440	CF16EL/BR30/827/BL	65	16	750	2700K	82	8,000	✓
		29573	CF16EL/BR30/827/CVP	65	16	750	2700K	82	8,000	✓
		29566	CF16EL/BR30/827/RP	65	16	750	2700K	82	8,000	✓
		29590	CF16EL/BR30/830	65	16	750	3000K	82	8,000	✓
		26931	CF16EL/BR30/835/RP	65	16	750	3500K	82	8,000	✓
	PAR38 	29140	CF23EL/PAR38/GL/830	75	23	1000	3000K	82	8,000	✓
		29731	CF23EL/PAR38/GL/830/DIS	75	23	1000	3000K	82	8,000	✓
		26935	CF23EL/PAR38/865/RP	75	23	1100	6500K	82	8,000	✓
		29635	CF23EL/PAR38/830	75	23	1200	3000K	82	8,000	✓
		29359	CF23EL/PAR38/827	75	23	1250	2700K	82	8,000	✓
29625		CF23EL/PAR38/827/BL	75	23	1200	2700K	82	8,000	✓	
BR40 	28997	CF19EL/BR40/DIM/827/RP*	75	19	900	2700K	82	8,000	✓	
	26926	CF23EL/BR40/LS/827/BL†	90	23	1050	2700K	82	8,000	✓	
	29706	CF23EL/BR40/827/BL	90	23	1250	2700K	82	8,000	✓	
	29452	CF23EL/BR40/827/RP	90	23	1250	2700K	82	8,000	✓	
	29455	CF23EL/BR40/830	90	23	1250	3000K	82	8,000	✓	

† Living Spaces™

* Compatible with standard electronic incandescent dimmers

** Cold cathode technology

*** 2W during LED operation

CF034-INSERTR27

SYLVANIA is a registered trademark of OSRAM SYLVANIA Inc.
 SEE THE WORLD IN A NEW LIGHT is a registered trademark of OSRAM SYLVANIA Inc.
 ENERGY STAR is a registered trademark of the U.S. Government.
 DULUX is a registered trademark of OSRAM AG.
 Specifications subject to change without notice.

SEE THE WORLD IN A NEW LIGHT

SYLVANIA

