



STUDIO, THEATRE, TV & VIDEO

ANSI Code	Product Number	Ordering Abbreviation	Color Temp (K)	Watts	Volts	Base	Lumens	Avg Rated Life (hrs)	Bulb	Pkg Qty	Footnotes
EHD	54508	EHD	3000	500	120	G9.5	10600	2000	T4	12	
EHF	54510	EHF	3300	750	120	G9.5	20400	300	T5	12	
EHG	54512	EHG	3000	750	120	G9.5	15400	2000	T5	12	
EHP	58942	EHP	2900	300	120	R7s	5000	2500	T4	12	
EHR	58936	EHR	3000	400	120	R7s	7500	2000	T4	12	
EJG	54598	EJG	3200	750	120	R7s	20600	400	T3	12	60
EKB	54837	EKB	3200	420	120	G29.5	11000	75	T6	24	58
FAD	54574	FAD	3200	650	120	R7s	16500	100	T4	12	
FAL	58860	FAL	3200	420	120	R7s	11000	75	T4	24	24
FCB	54483	FCB	3200	600	120	R7s	16500	75	T4	24	
FCM	54442	FCM	3200	1000	120	R7s	28000	400	T3	12	60
FDA	54471	FDA	3200	400	120	R7s	10400	250	T4	12	24
FDB	54435	FDB	3200	1500	120	R7s	41200	400	T4	12	60
FDG	54387	64579 115-120V	3200	1000	120	R7s	33000	15	T4	12	12
FDN	54534	FDN	3200	500	120	R7s	12800	400	T2.5	12	60
FEL	54570	FEL	3200	1000	120	G9.5	27500	300	T6	12	
FEP	54515	FEP/240	3200	1000	240	G9.5	23000	150	T6	12	
FER	54571	FER	3200	1000	120	RX7s	27500	500	T6	12	
FEV	54441	FEV	3200	200	120	DC Bayonet	5500	50	T4	12	
FEX	54514	FEX/230	3200	2000	230	RX7s	50000	300	T8	12	11
FEX	54518	FEX/240	3200	2000	240	RX7s	50000	300	T8	12	
FEY	54559	FEY	3200	2000	120	RX7s	57400	400	T8	12	
FFJ	54488	FFJ	3200	600	120	R7s	16500	75	T4	24	24
FFM	58862	FFM	3200	420	120	R7s	11000	75	T4	24	24
FFT	54350	FFT	3200	1000	120	R7s	27000	300	T3	12	
FHM	54532	FHM	3200	1000	120	R7s	27300	300	T3	12	60
FKJ	54681	FKJ CP/71	3200	1000	230	G22	26000	200	T6	20	58
FKK	54699	FKK CP/73	3200	2000	230	G38	52000	400	T11	1	58
FKW	54711	FKW	3200	300	120	GY9.5	7800	200	T6	24	58
FLK	54589	FLK	3200	575	115	G9.5	16500	300	T5	12	188
FLK	54551	FLK/X 115V	3200	575	115	G9.5	10000	2000	T5	12	188
	54549	FLK PLUS HPR 575/115	3200	575	115	G9.5	16500	300	T6	12	187
FMR	54412	FMR	3000	600	120	GY9.35	12500	2000	T5	24	
FRG	54629	FRG	3200	500	120	GY9.35	13000	150	T6	24	58
FRK	54631	FRK	3200	650	120	GY9.5	16900	200	T7	24	58
FRL	54638	FRL CP/89	3200	650	230	GY9.5	16250	150	T7	25	58
FSH	54436	FSH	3200	125	120	G5.3	2500	200	T3	24	
FTK	54875	FTK	3200	500	120	GY9.5	12000	200	T6	24	58
FVL	54459	FVL	3200	200	120	GX5.3	5200	200	T4	24	
FVM	54900	FVM	3200	105	120	GX5.3	2250	250	T4	24	
GCA	54428	GCA	3200	250	120	G5.3	5700	200	T3	24	
GLA	54516	GLA 575/115/2000	3050	575	115	G9.5	10500	2000	T6	12	18

**Index by Ordering
Abbreviation (cont.)**

Type	Page
HMI 18000 W/SE/GX51	226
HPL 375/115 (UCF)	217
HPL 375/115/X (UCF)	217
HPL 550/77 (UCF)	217
HPL 550/77/X (UCF)	217
HPL 575/115 (UCF)	217
HPL 575/115/X (UCF)	217
HPL 575/120 (UCF)	217
HPL 575/120/X (UCF)	217
HPL 575/230 (UCF)	217
HPL 575/230/X (UCF)	217
HPL 575/240 (UCF)	217
HPL 575/240/X (UCF)	217
HPL 750/77 (UCF)	217
HPL 750/115 (UCF)	217
HPL 750/115/X (UCF)	217
HPL 750/120 (UCF)	217
HPL 750/120/X (UCF)	217
HPL 750/230 (UCF)	217
HPL 750/230/X (UCF)	217
HPL 750/240 (UCF)	217
HPL 750/240/X (UCF)	217
HSD 150W/70 4ARXS	236
HSD 150W/UL/75 4ARXS	236
HSD 200W/60 4ARXS	236
HSD 250W/60 4ARXS	236
HSD 250W/80 4ARXS	236
HSD 250W/UL/75 4ARXS	236
HSD 575W/60 4ARXS	236
HSD 575W/72 4ARXS	236
HSD 575W/UL/75 4ARXS	236
HSR 400/60	235
HSR 575/60	235
HSR 575/72	235
HSR 700/60	235
HSR 1200/60	235
HTI S 35/12	229
HTI 150 W	229
HTI 152 W	229
HTI 250 W/22	234
HTI 250 W/32	234
HTI 250 W/32C	234
HTI 250W/D5/80 BABY SHARXS	232
HTI 300 W/DX	233
HTI 300W/D5/57 BABY SHARXS	232
HTI 300W/D5/65 BABY SHARXS	232
HTI 400 W/24	234
HTI 400W/D3/75 SHARXS	230
HTI 400W/D3/75 SHARXS BULK	230
HTI 400W/D5/60 BABY SHARXS	232
HTI 403 W/24	234
HTI 405 W/SE XS	229
HTI 575W/D4/60 SHARXS	230
HTI 575W/D4/75 SHARXS	230
HTI 575W/D5/56 BABY SHARXS	232
HTI 600 W/SE	229
HTI 700 W/SE/75	229
HTI 700W/D4/60 SHARXS	230
HTI 700W/D4/60 SHARXS BULK	230
HTI 700W/D4/75 SHARXS	231
HTI 700W/D4/75 SHARXS BULK	231
HTI 705 W/SE XS	229
HTI 1200 W/SE XS	229
HTI 1200W/D7/60 SHARXS	231
HTI 1200W/D7/60 SHARXS BULK	231
HTI 1200W/D7/75 SHARXS	231
HTI 1500W/D7/60 SHARXS	231
HTI 1800W/SE XS	229
HTI 2500 W/DEL	233
HTI 2500 W/SE XS	229
HTI 4000 W/DE	233
HWWL 1200W/80V	217
HWMV 1200W/115V	217
HWHV 1200W/220V	217
HXP R 120 W/17C	257
HXP R 120 W/45 C UV	257
HXP R 120 W/45 C VIS	257
JCP 650W/100V	215
LX24T3/956/A4	270
LX40T3/956/A3	270

Type	Page
Na 10 FL	269
Na/10	269
Q4559	220
Q4559X	220
Q4681	220
QXL 750/77	218
QXL 750/77/X	218
STUDIOLINE 55W/3200	218
STUDIOLINE 55W/5600	218
VIP R 273/45	268
XBO 75 W/2	237
XBO 75 W/2 OFR	237
XBO 100 W OFR	237
XBO R 100 W/45 OFR	237
XBO R 100 W/45C OFR	237
XBO R 101 W/45C OFR	238
XBO 150 W/1	238
XBO 150 W/1 OFR	238
XBO 150 W/4	238
XBO 150 W/CR OFR	238
XBO 150 W/S	239
XBO R 180 W/45/OFR	239
XBO R 180 W/45C OFR	239
XBO R 181 W/45C OFR	239
XBO R 300 W/60C OFR	239
XBO 450 W	240
XBO 450 W OFR	240
XBO 450 W/1	240
XBO 450 W/2 OFR	240
XBO 450 W/4	240
XBO 500 W/H OFR	241
XBO 700 W/HS OFR	241
XBO 900 W OFR	241
XBO 1000 W/HS OFR	241
XBO 1000 W/HSC OFR	241
XBO 1000 W/HTP OFR	242
XBO 1600 W OFR	242
XBO 1600 W/CA OFR	242
XBO 1600 W/HS OFR	242
XBO 1600 W/HSC OFR	242
XBO 2000 W/DTP OFR	243
XBO 2000 W/H CL OFR	243
XBO 2000 W/H OFR	243
XBO 2000 W/H XL OFR	243
XBO 2000 W/HCC OFR	243
XBO 2000 W/HPS OFR	244
XBO 2000 W/HS OFR	244
XBO 2000 W/HTP OFR	244
XBO 2000 W/SHSC OFR	244
XBO 2001 W/HTP OFR	244
XBO 2500 W OFR	245
XBO 2500 W/HS OFR	245
XBO 2500 W/HTP OFR	245
XBO 3000 W/DHP OFR	245
XBO 3000 W/DHS OFR	245
XBO 3000 W/DTP OFR	246
XBO 3000 W/H CL OFR	246
XBO 3000 W/H OFR	246
XBO 3000 W/H XL OFR	246
XBO 3000 W/HPS OFR	246
XBO 3000 W/HS CL OFR	247
XBO 3000 W/HS OFR	247
XBO 3000 W/HS XL OFR	247
XBO 3000 W/HSLA OFR	247
XBO 3000 W/HTP OFR	247
XBO 4000 W/DHP OFR	248
XBO 4000 W/HS CL OFR	248
XBO 4000 W/HS OFR	248
XBO 4000 W/HS XL OFR	248
XBO 4000 W/HTP OFR	248
XBO 4200 W/CA OFR	249
XBO 4200 W/GS OFR	249
XBO 4200 W/HPS OFR	249
XBO 4500 W/DHP OFR	249
XBO 4500 W/DTP OFR	249
XBO 4500 W/HS OFR	250
XBO 4500 W/HSLA OFR	250
XBO 4500 W/HTP OFR	250
XBO 5000 W/H OFR	250
XBO 5000 W/HTP OFR	250
XBO 6000 W/DHP OFR	251
XBO 6000 W/DTP OFR	251
XBO 6000 W/HS OFR	251

Type	Page
XBO 6000 W/HSLA OFR	251
XBO 6000 W/HTP OFR	251
XBO 6500 W/DHP OFR	252
XBO 6500 W/HSLA OFR	252
XBO 7000 W/HS OFR	252
XBO 8000 W/HS OFR	252
XERADEX 20	270
XERADEX 20/HV	270
XERADEX 20/SY45/45	270
Xstage 2000W OFR	253
Xstage 3000W OFR	253
Xstage 4000W OFR	253
Xstage 7000W OFR	253

Type	Page
11558	211
11560	211
11619	211
11624	217
11625	217
11655	215
11656	217
11657	217
13365	211
14936	220
14974	219
14988	220
14994	220
15399	220
17980	220
17981	220
20607	218
20608	218
52079	270
52155	270
53997	215
53999	214
54001	217
54021	214
54022	214
54028	214
54032	219
54038	211
54044	213
54050	214
54061	225
54062	225
54063	225
54066	227
54067	225
54068	227
54070	226
54071	227
54073	228
54074	228
54078	229
54079	229
54080	234
54081	234
54083	234
54087	229
54088	227
54089	234
54098	227
54099	226
54102	235
54104	234
54107	235
54113	226
54115	235
54116	235
54121	214
54122	214
54123	211
54124	214
54125	214
54126	211
54129	236
54130	229
54133	233
54137	225
54138	214
54139	229
54141	229
54142	229
54143	233
54167	236
54168	235
54170	236
54189	211
54192	211
54202	231
54210	211
54211	211
54212	212

Type	Page
54214	214
54231	211
54232	217
54233	214
54241	230
54242	231
54243	236
54245	214
54246	213
54247	214
54248	213
54249	211
54250	211
54251	212
54252	214
54253	213
54254	211
54255	212
54256	213
54257	214
54258	214
54259	212
54260	212
54261	212
54262	214
54263	213
54264	213
54265	227
54268	231
54269	231
54270	230
54271	236
54272	211
54273	214
54274	214
54275	214
54276	213
54277	213
54278	214
54280	230
54281	231
54282	230
54283	230
54287	236
54288	236
54289	226
54296	230
54297	232
54298	232
54299	232
54300	232
54301	214
54302	214
54303	214
54310	225
54311	236
54312	236
54313	227
54314	227
54315	228
54316	228
54317	228
54319	231
54321	226
54329	229
54350	216
54354	214
54356	214
54357	226
54359	232
54366	212
54383	213
54386	213
54387	216
54388	212
54392	212
54394	212
54399	233
54400	213
54409	211
54411	211
54412	216
54428	216