

Product Number: 13647

Order Abbreviation: 25B10C/BL/4PK 120V

General Description: Incandescent Clear B10 25 Watt 120 Volt Candelabra Base 4 Pack Blister Pack

Product Information	
Abbrev. With Packaging Info.	25B10CBL4PK 120V 24/CS 4/SKU
Average Rated Life (hr)	1500
Base	Candelabra
Bulb	B10
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	1.250
Diameter (mm)	31.75
Filament	C-7A
Lamp Finish	Clear
Maximum Overall Length - MOL (in)	3.875
Maximum Overall Length - MOL (mm)	98.425
Nominal Voltage (V)	120.00
Nominal Wattage (W)	25.00