



DULUX® EL SELF-BALLASTED COMPACT FLUORESCENT LAMPS

Twist Compact Fluorescent Lamps

Nominal Wattage	Bulb	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Avg Rated Life (hrs)	CCT (K)	CRI	Approx Lumens Initial @25°C/77°F	Approx Lumens Mean @25°C/77°F	Symbols & Footnotes
27	TWIST	6.1	Medium	29390	CF27EL/TWIST/830	120	6	10000	3000	82	1750	1400	☑ ☑ ☑ 1,3,8, 9,12,14,20
30	TWIST	5.13	Medium	29395	CF30EL/TWIST/830	120	6	10000	3000	82	2000	1600	☑ ☑ ☑ 1,3,8, 9,12,14,20
				29392	CF30EL/TWIST/830/BL	120	5	6000	3000	82	2000	1600	☑ ☑ ☑ 1,3,8, 9,12,14,20
				29415	CF30EL/TWIST/827	120	6	10000	2700	82	2000	1600	☑ ☑ ☑ 1,3,8, 9,12,14,20
40	TWIST	5.25	Medium	29147	CF40EL/TWIST/827	120	6	8000	2700	82	2600	2080	☑ ☑ ☑ 1,3,8, 9,12,14,20
				29481	CF40EL/TWIST/830/BL	120	10	6000	3000	82	2600	2080	☑ ☑ ☑ 1,3,8, 9,12,14,20
65	TWIST	7.85	Medium	29508	CF65EL/TWIST/841	120	6	8000	4100	82	4200	3360	☑ ☑ ☑ 1,3,8, 9,12,14,20
12 19 28	TWIST	5.75	3CON Med	29523	CF28EL/3WAY/TWIST/827	120	6	6000	2700	82	600 1100 1800	480 880 1440	☑ ☑ ☑ 1,3,8, 9,12,14,20
				29351	CF28EL/3WAY/TWIST/830	120	6	6000	3000	82	600 1100 1800	480 880 1440	☑ ☑ ☑ 1,3,8, 9,12,14,20
				29349	CF28EL/3WAY/TWIST/830/BL	120	5	6000	3000	82	600 1100 1800	480 880 1440	☑ ☑ ☑ 1,3,8, 9,12,14,20

Classic (A-shape) Compact Fluorescent Lamps

Nominal Wattage	Bulb	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Avg Rated Life (hrs)	CCT (K)	CRI	Approx Lumens Initial @25°C/77°F	Approx Lumens Mean @25°C/77°F	Symbols & Footnotes
5	A15	3.95	Medium	29743	CF5EL/A15/DIM/830	120	6	15000	3000	82	200	160	☑ ☑ ☑ 1,3,8, 12,14,20
9	A19	4	Medium	29665	CF9EL/A19/827	120	6	8000	2700	82	450	360	☑ ☑ ☑ 1,3,8, 9,12,14,20
	A15	4	Medium	29526	CF9EL/A15/830/BL2	120	12	8000	3000	82	450	360	☑ ☑ ☑ 1,3,8, 9,12,14,20
14	A19	4.75	Medium	29575	CF14EL/A19/827	120	6	6000	2700	82	800	640	☑ ☑ ☑ 1,3,8, 9,12,14,20
				29468	CF14EL/A19/830	120	6	6000	3000	82	800	640	☑ ☑ ☑ 1,3,8, 9,12,14,20
	5	Medium	29485	CF14EL/A19/830/BL	120	6	8000	3000	82	800	640	☑ ☑ ☑ 1,3,8, 9,12,14,20	
			29346	CF14EL/A19/Y/BL	120	5	6000	-	-	405	324	☑ ☑ ☑ 1,3,8, 9,12,14,20	

Decorative Compact Fluorescent Lamps

Nominal Wattage	Bulb	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Avg Rated Life (hrs)	CCT (K)	CRI	Approx Lumens Initial @25°C/77°F	Approx Lumens Mean @25°C/77°F	Symbols & Footnotes
4	FLAME	4.25	Candelabra	29135	CF4EL/B15/C/827	120	6	6000	2700	82	160	128	☑ ☑ ☑ 1,3,8, 9,12,14,20
				29121	CF4EL/B15/C/830/BL	120	6	6000	3000	82	160	128	☑ ☑ ☑ 1,3,8, 9,12,14,20