



S11

C7 Candelabra

S6

S14

A15

A21

T6

T7

T10

GENERAL PURPOSE LAMPS

Watts	Bulb	Base	Product Number	Symbols & Footnotes	Ordering Abbreviation	Volts	Pkg Qty	Description	Class & Filament	Avg Rated Life (hrs)	Lumens Beam Angle CBCP	LCL (in)	MOL (in)
7.5	S11	Med	19423		7.5S/CR	120	120	Ceramic Red	B, C-9	1400			2.25
10	C7	Candelabra	13636		10C7/CL	120	240	Clear Pilot Light Vibration Resistant	B, C-7A		38		2.13
	S6	Candelabra	16726		10S6	120	240	Clear Indicator	B, C-7A	1500	71	1.44	1.88
			16717		10S6230V	230	240	Clear Indicator	B, CC-7A	1500	65	1.44	1.88
	S11	Intermediate	16917		10S11N/CL	120	120	Clear Vibration Resistant	B, C-7A	1500	74	1.63	2.31
			16919		10S11N/CL	130	120	Clear Vibration Resistant	B, C-7A	1500	74	1.63	2.31
	S14	Med Brass	17406		10S14	120	120	Clear Vibration Resistant	B, C-9	1500	76	2.50	3.50
11	S14	Med Brass	17448		11S14	120	120	Clear Vibration Resistant	B, C-9	3000	74	2.50	3.50
			17450		11S14	130	120	Clear Vibration Resistant	B, C-9	3000	72	2.50	3.50
			17453		11S14/IF	130	120	Inside Frost Vibration Resistant	B, C-9	3000	68	2.50	3.50
			17487		11S14/TR	130	120	Transparent Red	B, C-9	3000		2.50	3.50
12	S6	Candelabra	16718		12S6/250V	250	240	Clear Indicator	B, CC-7A	1500	61	1.44	1.88
15	A15	Med	10015		15A15/W/RP	120	24	White Utility Light	C, C-9	2500	65	2.38	3.50
			10018		15A15/CL	120	120	Clear Utility Light	B, C-9	2500	105	2.38	3.50
			10028		15A15/CL/RP	120	24	Clear Utility Light	B, C-9	2500	105	2.38	3.50
			10019		15A15/CL <i>@ 120_volts, approximate 13 watts, 80 lumens, 6250 hours.</i>	130	120	Clear Utility Light	B, C-9	2500	105	2.38	3.50
			10037		15A15	120	120	Inside Frost	B, C-9	2500	100	2.38	3.50
			10031		15A15/RP	120	24	Inside Frost	B, C-9	2500	100	2.38	3.50
			10038		15A15 <i>@ 120_volts, approximate 13 watts, 76 lumens, 6250 hours.</i>	130	120	Inside Frost	B, C-9	2500	100	2.38	3.50
15 135 150	A21	3 CONTACT Med	18009		15/150A/SECURITYLIGHT	120	12	Soft White Security 3-way	C, CC-8	1200	800m 2070lm 2150lm	3.38	5.31
15	S11	Med	17079		15S11/102/IF	120	120	Inside Frost Refrigerator	B, C-7A	400	138	1.56	2.25
	S14	Med Brass	17240		15S14/CL	130	120	Clear Vibration Resistant Sign	B, C-9	3000	106	2.50	3.50
	T6	Candelabra	18037		15T6	120	60	Clear Tubular	B, C-7A	2000	111		3.06
			18038		15T6	130	60	Clear Tubular	B, C-7A	2000	105		3.06
			18078		15T6/145V	145	60	Clear Tubular	B, C-7A	2000	112		3.06
			18036		15T6/BL	145	12	Clear Tubular	B, C-7A	2000	112		3.06
	T7	Candelabra	18185		15T7C	120	60	Clear	B, C-7A	1000	111	1.50	2.25
		DC Bayonet	18208		15T7DC	120	60	Clear	B, C-7A	1000	111	1.31	2.25
			18200		15T7DC/BL	120	12	Clear Carded	B, C-7A	1000	111	1.31	2.25
			18201		15T7DC/BL/1/6	120	6	Clear Carded	B, C-7A	1000	111	1.31	2.25
		Intermediate	18173		15T7N	120	60	Clear	B, C-7A	1000	115	1.56	2.25
			18174		15T7N/BL	120	12	Clear	B, C-7A	1000	115	1.56	2.25
	T10	Med	18501		15T10/CL	120	60	Clear Tubular	B, C-8	2500	112		5.63