



GENERAL PURPOSE LAMPS

Watts	Bulb	Base	Product Number	Symbols & Footnotes	Ordering Abbreviation	Volts	Pkg Qty	Description	Class & Filament	Avg Rated Life (hrs)	Lumens Beam Angle CBCP	LCL (in)	MOL (in)
250	R40	Med	14663	★ ^{24,46,57,155}	250R40/10	120	6	Red Bowl IR Heat Lamp Reflector Hard Glass	C, C-6	5000			6.88
300	BR40	Med Brass	14779	^{2,46,57,155}	300BR/FL	120	24	Reflector Flood	C, CC-2V	2000	3030lm 2900 cd 60°		6.50
	PAR56	Mog End Prong	14947	★ ^{117,188}	300PAR56/NSP	120	12	Narrow Spot	C, CC-13	2000	3840lm 68000 cd 8x10 VH		5.00
			14944	★ ^{117,188}	300PAR56/NSP	130	12	Narrow Spot	C, CC-13	2000	3840lm 68000 cd 8x10 VH		5.00
			14950	★ ^{117,188}	300PAR56/MFL	120	12	Med Flood	C, CC-13	2000	3840lm 24000 cd 11x25 VH		5.00
			14946	★ ^{117,188}	300PAR56/MFL	130	12	Med Flood	C, CC-13	2000	3840lm 24000 cd 11x25 VH		5.00
			14953	★ ^{117,188}	300PAR56/WFL	120	12	Wide Flood	C, CC-13	2000	3840lm 11000 cd 20x35 VH		5.00
			14945	★ ^{117,188}	300PAR56/WFL	130	12	Wide Flood	C, CC-13	2000	3840lm 11000 cd 20x35 VH		5.00
	Screw Term		14967	★ ^{117,188}	25A/PAR56/WFL	12	12	Swimming Pool	C, C-6	1000	6000lm 15x40 VH		4.50
	PS30	Med	15742	●	300M/CL	120	60	Clear Utility Light	C, C-9	750	5870	6.00	8.06
			15740	●	300M/CL/RP	120	12	Clear Utility Light	C, C-9	750	5870	6.00	8.06
			15744	● ^{29,136}	300M/CL <i>@ 120_volts, approximate 264 watts, 4390 lumens, 1875 hours</i>	130	60	Clear Utility Light	C, C-9	750	5820	6.00	8.06
			15737	●	300M/IF	120	60	Inside Frost Utility Light	C, C-9	750	5860	6.00	8.06
			15735	●	300M/IF/RP	120	12	Inside Frost Utility Light	C, C-9	750	5860	6.00	8.06
			15739	● ^{29,136}	300M/IF <i>@ 120_volts, approximate 264 watts, 4390 lumens, 1875 hours</i>	130	60	Inside Frost Utility Light	C, C-9	750	5760	6.00	8.06
			15738	● ²⁹	300M/IF/CVP/6 <i>@ 120_volts, approximate 264 watts, 4390 lumens, 1875 hours</i>	130	6	Inside Frost Utility Light	C, C-9	750	5760	6.00	8.06
	Med Brass		15761	● ^{27,136}	300M/IF/99/XL <i>@ 120_volts, approximate 264 watts, 3800 lumens, 6250 hours</i>	130	60	Inside Frost Excel-Line	C, C-9	2500	4990	6.00	8.06
	PS35	Mogul	15904		300PS35/CL/99/XL	120	24	Clear Excel-Line	C, C-9	2500	5190	7.00	9.38
			15930		300PS35/99IF/XL	130	24	Inside Frost Excel-Line	C, C-9	2500	5070	7.00	9.38
			15915		300PS35/CL	120	24	Clear Utility Light	C, C-9	1000	5700	7.00	9.38
			15917		300PS35/CL	130	24	Clear Utility Light	C, C-9	1000	5250	7.00	9.38
			15918		300PS35/IF	120	24	Inside Frost Utility Light	C, C-9	1000	5700	7.00	9.38
			15920		300PS35/IF	130	24	Inside Frost Utility Light	C, C-9	1000	5250	7.00	9.38
			16068		300PS35/CL	277	24	Clear	C, C-7A	1000	4220	7.00	9.38
375	R40	Med Skirted	14747	★ ^{24,46}	375R40/1	120	24	Reflector IR Heat Lamp Clear	C, C-11	5000			7.63