



PS25



PS35



A19



A21



A23

DECORATIVE LAMPS

Watts	Bulb	Base	Product Number	Symbols & Footnotes	Ordering Abbreviation	Volts	Pkg Qty	Description	Class & Filament	Avg Rated Life(hrs)	MOL (in)
150	PS25	Med	15271	●	150PS25/SB	120	60	Silver Bowl	C, C-9	1000	6.94
300	PS35	Mogul	15958		300PS35/SB/IF	120	24	Silver Bowl Inside Frost Brass Base	C, C-9	1000	9.38

TRAFFIC SIGNAL LAMPS

Watts	Bulb	Base	Product Number	Symbols & Footnotes	Ordering Abbreviation	Volts	Pkg Qty	Description	Class & Filament	Avg Rated Life(hrs)	Approx Lumens	LCL (in)	MOL (in)
54	A19	Med Brass	10441	▼ _{96,130}	54A19TS/8M/SS	120	120	Clear Traffic Signal KR Filled w/ Heat Reflector	C, C-11V	8000	515	2.44	4.44
60	A19	Med Brass	10442	▼ _{96,130}	60A19TS/8M/SS 120-	120	120	Clear Traffic Signal KR Filled w/ Heat Reflector	C, C-11V	8000	595	2.44	4.44
67	A21	Med Brass	12570	▼ ₉₆	67A21/40/8M	120	24	Clear Traffic Signal	C, C-9	8000	610	2.44	4.44
			12562	▼ ₉₆	67A21/40/8M	130	120	Clear Traffic Signal	C, C-9	8000	610	2.44	4.44
			12572	▼ ₉₆	67A21/40/8M	130	24	Clear Traffic Signal	C, C-9	8000	610	2.44	4.44
69	A21	Med Brass	12496	▼ ₉₆	69A21/TS/8M	120	24	Clear Traffic Signal	C, C-9	8000	640	2.44	4.44
			12497	▼ ₉₆	69A21/TS/8M	125	24	Clear Traffic Signal	C, C-9	8000	665	2.44	4.44
			12498	▼ ₉₆	69A21/TS/8M	130	24	Clear Traffic Signal	C, C-9	8000	640	2.44	4.44
90	A19	Med Brass	12299	▼ _{96,130}	90A19/1/TS/8M/SS 120-	120	120	Clear Traffic Signal KR Filled w/ Heat Reflector	C, C-11V	8000	1000	3.00	4.44
			11151	▼★ _{96,130}	90A19/TS/8M/SS	120	120	Clear Traffic Signal KR Filled w/ Heat Reflector	C, C-11V	8000	1000	2.44	4.44
101	A23	Med Brass	13305	▼ ₉₆	101A23/6M	120	120	Inside Frost Traffic Signal	C, C-9	6000	900	4.38	6.06
116	A21	Med Brass	12833	▼ ₉₆	116A21/TS/8M	120	24	Clear Traffic Signal	C, C-9	8000	1260	2.44	4.44
			12817	▼ ₉₆	116A21/TS/8M	130	24	Clear Traffic Signal	C, C-9	8000	1260	2.44	4.44
135	A21	Med Brass	12843	▼ _{96,130}	135A21/TS/8M/SS 120-	120	24	Clear Traffic Signal KR Filled w/ Heat Reflector	C, C-11V	8000	1750	3.00	4.44
170	A23	Med Brass	15017	▼ ₉₆	1950L/A23/8M	120	60	Clear Traffic Signal	C, C-9	8000	1950	3.00	4.75
			15021	▼ ₉₆	1950L/A23/8M	130	60	Clear Traffic Signal	C, C-9	8000	1950	3.00	4.75