



T10



A15



A21



R20



S11



A19

## GENERAL PURPOSE LAMPS

Watts	Bulb	Base	Product Number	Symbols & Footnotes	Ordering Abbreviation	Volts	Pkg Qty	Description	Class & Filament	Avg Rated Life (hrs)	Lumens Beam Angle CBCP	LCL (in)	MOL (in)	
25	T10	Med	18491	●	<b>25T10/CL/BL/6PK</b>	120	6	Clear	B, C-8	1000	232		5.63	
			18512	●	<b>25T10</b>	130	60	Clear	B, C-8	1000	232		5.63	
			18503	●	<b>25T10/F</b>	120	60	Inside Frost	B, C-8	1000	230		5.63	
			18492	●	<b>25T10/F/BL/6PK</b>	120	6	Inside Frost	B, C-8	1000	230		5.63	
			18505	●	<b>25T10/F</b>	130	60	Inside Frost	B, C-8	1000	230		5.63	
30	A15	Med Brass	10122		<b>30A15</b>	130	120	Inside Frost	C, C-9	2000	200	2.38	3.50	
<i>@ 120_volts, approximate 26 watts, 150 lumens, 5000 hours.</i>														
30 70 100	A21	3 CONTACT Med	19395	●	<b>30/100/DAYLIGHT/1/12</b>	120	12	Daylight 3-Way	C, CC-8	1200	220lm 700lm 920lm	3.38	5.31	
			19345	●	<b>30/100A21/DL/SW/1/48</b>	120	48	Soft White Double Life 3-Way	C, CC-8	2400	270lm 860lm 1130lm	3.38	5.31	
			19380	●	<b>30/100A21/DL/SW/RP</b>	120	12	Soft White Double Life 3-way	C, CC-8	2400	270lm 860lm 1130lm	3.38	5.31	
			18029	●	<b>30/100A/W/DIYPACK</b>	120	48	Soft White 3-way	C, CC-8	1200	300lm 945lm 1245lm	3.38	5.31	
			19385	●	<b>30/100A21/W/RP</b>	120	12	Soft White 3-way	C, CC-8	1200	300lm 945lm 1245lm	3.38	5.31	
30	R20	Med Brass	14794		<b>30R20</b>	120	60	Reflector Flood	C, C-9	2000	140 40°		3.94	
			14836		<b>30R20/RP</b>	120	6	Reflector Flood	C, C-9	2000	140 40°		3.94	
			14802		<b>30R20</b>	130	60	Reflector Flood	C, C-9	2000	140 40°		3.94	
			<i>@ 120_volts, approximate 26 watts, 100 lumens, 5000 hours</i>											
	S11	DC Bayonet	10765		<b>30S11/DC/75V</b>	75	120	Clear Train Marker	C, C-7A	500	284	1.50	2.38	
32	A19	Med Brass	10983	●	<b>32A19/49</b>	130	120	Clear Street Lighting Group Replacement	C, C-9	3000	258	2.88	4.25	
<i>@ 120_volts, approximate 28 watts, 200 lumens, 7500 hours.</i>														
34	A19	Med	11391	●	<b>40A/34/W/ES/4PK</b>	120	48	Soft White Energy Saver	C, CC-8	1500	375	3.13	4.44	
			11058	●	<b>40A/34/SS</b>	120	48	Standard Frost SuperSaver	C, CC-8	1500	375	3.13	4.44	
			11379	●	<b>40A/34/SS</b>	130	48	Standard Frost SuperSaver	C, CC-8	1500	380	3.13	4.44	
	<i>@ 120_volts, approximate 30 watts, 290 lumens, 3750 hours</i>													
		Med Brass	11383		<b>40A/34/SS/XL</b>	120	48	Standard Frost SuperSaver XL	C, CC-8	2500	310	3.13	4.44	
	11387			<b>40A/34/SS/XL</b>	130	48	Standard Frost SuperSaver XL	C, CC-8	2500	310	3.13	4.44		
<i>@ 120_volts, approximate 30 watts, 240 lumens, 6250 hours</i>														
40	A15	Candelabra	11534		<b>40A15C/SW/FAN/2/12/BL</b>	120	12	Soft White Ceiling Fan Light	C, C-9	1000	300	1.94	3.38	
			10029		<b>40A15C/CL/FAN/2/12/BL</b>	120	12	Clear Ceiling Fan	C, C-9	1000	330	1.94	3.38	
		Med	10181	●	<b>40A15/DAY/FAN/BL/2/24</b>	120	24	Daylight Fan	C, C-9	1000	340	2.38	3.50	
	11664		●	<b>40A15/DL/SW/FAN/BL/2/24</b>	120	24	Soft White Double Life Fan	C, C-9	2000	310	2.38	3.50		
	10061		●	<b>40A15/CL/DL/APPL/2/12/BL</b>	120	12	Clear Double Life Appliance	C, C-9	2000	350	2.38	3.50		