



PAR16 GU10



PAR16 GU10



PAR20

CAPSYLITE® PAR16 LAMPS

Suitable for use in unshielded fixtures.

Watts	Bulb	Base	Product Number	Symbols & Footnotes	Ordering Abbreviation	Volts	Pkg Qty	Beam Type	Class & Filament	Avg Rated Life (hrs)	Lumens CCT	CBCP	Beam Angle	MOL (in)			
50	PAR16	GU10	59061	72	50PAR16/HAL/GU10/FL/BL3	120	18	FL	C,CC-8	3000	450 2800	800	30	2.25			
			59075	72	50PAR16/HAL/GU10/FL/BL	120	6	FL	C,CC-8	3000	450 2800	800	30	2.25			
			59024	68	50PAR16/HAL/GU10/FL40	120	10	FL	C,CC-2V	1000	400 2950	640	40	2.08			
			59020	68	50PAR16/HAL/GU10/FL/CLAM	120	6	FL	C,CC-2V	1000	400 2950	640	40	2.08			
60	PAR16	E26 Med	59032	69,118	60PAR16/HAL/NSP10	120	15	NSP	C,CC-8	2000	650 2850	5000	10	2.88			
			59037	69,118	60PAR16/HAL/NSP10/RP	120	6	NSP	C,CC-8	2000	650 2850	5000	10	2.88			
			59040	69,118,137,169	60PAR16/HAL/NSP10	130	15	NSP	C,CC-8	2000	650 2850	5000	10	2.88			
			@ 120 volts, approximate 53 watts, 495 lumens, 4000 hours														
			59030	69,118	60PAR16/HAL/NFL30	120	15	NFL	C,CC-8	2000	650 2850	1300	30	2.88			
			59031	69,118	60PAR16/HAL/NFL30/RP	120	6	NFL	C,CC-8	2000	650 2850	1300	30	2.88			
75	PAR16	E26 Med	59036	69,118	75PAR16/HAL/NSP10	120	15	NSP	C,CC-8	2000	900 2900	7500	10	2.88			
			59044	69,118,137,180	75PAR16/HAL/NSP10	130	15	NSP	C,CC-8	2000	900 2900	7500	10	2.88			
			@ 120 volts, approximate 66 watts, 685 lumens, 4000 hours														
			59034	69,118	75PAR16/HAL/NFL30	120	15	NFL	C,CC-8	2000	900 2900	1900	30	2.88			
			59033	69,118	75PAR16/HAL/NFL30/RP	120	6	NFL	C,CC-8	2000	900 2900	1900	30	2.88			
59042	69,118,137,180	75PAR16/HAL/NFL30	130	15	NFL	C,CC-8	2000	900 2900	1900	30	2.88						
@ 120 volts, approximate 66 watts, 685 lumens, 4000 hours																	

CAPSYLITE IR® PAR20

Halogen PAR lamp with infrared reflective coating on the lamp capsule. Suitable for use in unshielded fixtures.

Watts	Bulb	Base	Product Number	Symbols & Footnotes	Ordering Abbreviation	Volts	Pkg Qty	Beam Type	Class & Filament	Avg Rated Life (hrs)	Lumens CCT	CBCP	Beam Angle	MOL (in)
40	PAR20	E26 Med	14164	43,47,118	40PAR20/CAPIR/NSP10	120	15	NSP	C,CC-8	4000	510 2750	4200	10	3.25
			14166	43,47,118	40PAR20/CAPIR/NFL30	120	15	NFL	C,CC-8	4000	510 2750	1100	30	3.25
			14130	43,47,118	40PAR20/CAPIR/WFL40	120	15	WFL	C,CC-8	4000	510 2750	800	40	3.25