

SYLVANIA CONFIDENTIAL NET PRICES

Effective May 1, 2012

VENDOR ID. NO. DCI 046135 UPC 46135	ORDERING ABBREVIATION	STD CASE QTY	S T K	DIST STOCK COST	SUGG USER PRICE
OS Item No.					


VENDOR ID. NO. DCI 046135 UPC 46135	ORDERING ABBREVIATION	STD CASE QTY	S T K	DIST STOCK COST	SUGG USER PRICE
OS Item No.					

Bipin (T-8,T-12)

22529	F25T12/CW/33.....	30	C	13.30	24.48
22333	F25T12/WW/30.....	30	C	16.69	30.71
23116	F30T8/CW.....	24	Ⓟ B	9.15	15.20
23121	F30T8CW 6/cs.....	6	Ⓟ C	10.63	19.55
23100	F30T8/D.....	24	C	11.93	21.96
23701	F30T8/WW.....	24	C	11.57	21.29

Fluorescent Dulux


DULUX® S (Single)



21279	CF5DS/827/ECO.....	50	C	•	•
21278	CF5DS/841/ECO.....	50	C	•	•
21277	CF7DS/827/ECO.....	50	A	•	•
21276	CF7DS/835/ECO.....	50	A	•	•
21274	CF7DS/841/ECO.....	50	A	•	•
21275	CF7DS/850/ECO.....	50	A	•	•
21272	CF9DS/827/ECO.....	50	A	•	•
21273	CF9DS/835/ECO.....	50	A	•	•
21270	CF9DS/841/ECO.....	50	A	•	•
21271	CF9DS/850/ECO.....	50	A	•	•
Value Added Product					
20534	☀️ CF13DS/827/CVP.....	10	Ⓟ C	•	•
21136	CF13DS/827/ECO.....	50	A	•	•
21133	CF13DS/830/ECO.....	50	A	•	•
21137	CF13DS/835/ECO.....	50	A	•	•
21134	CF13DS/841/ECO.....	50	A	•	•
21135	CF13DS/850/ECO.....	50	A	•	•
21251	DULUX S 9W/78.....	50	C	•	•

Fluorescent Dulux

DULUX® S/E (Single)



20315	CF5DS/E/841.....	50	C	•	•
20312	CF7DS/E/827.....	50	C	•	•
20316	CF7DS/E/841.....	50	C	•	•
20313	CF9DS/E/827.....	50	C	•	•
20317	CF9DS/E/841.....	50	C	•	•
20314	CF13DS/E/827.....	50	C	•	•
20284	CF13DS/E/830.....	50	C	•	•
20318	CF13DS/E/841.....	50	C	•	•

Fluorescent Dulux


DULUX® D (Double)



21122	CF9DD/827/ECO.....	50	C	•	•
21097	CF9DD/827/RP/ECO.....	10	Ⓟ C	•	•
21121	CF9DD/830/ECO.....	50	C	•	•
21123	CF9DD/835/ECO.....	50	C	•	•
21117	CF13DD/827/ECO.....	50	C	•	•
21119	CF13DD/830/ECO.....	50	C	•	•
21118	CF13DD/835/ECO.....	50	C	•	•
21120	CF13DD/841/ECO.....	50	C	•	•
21109	CF18DD/827/ECO.....	50	C	•	•
21112	CF18DD/830/ECO.....	50	C	•	•
21110	CF18DD/835/ECO.....	50	C	•	•
21111	CF18DD/841/ECO.....	50	C	•	•
21113	CF26DD/827/ECO.....	50	C	•	•
21116	CF26DD/830/ECO.....	50	C	•	•
21114	CF26DD/835/ECO.....	50	C	•	•
21115	CF26DD/841/ECO.....	50	C	•	•

Fluorescent Dulux


DULUX® D/E (Double)



20682	CF13DD/E/827/ECO.....	50	C	•	+	•
20721	CF13DD/E/830/ECO.....	50	C	•	+	•
20671	CF13DD/E/835/ECO.....	50	C	•	+	•
20667	CF13DD/E/841/ECO.....	50	C	•	+	•
20683	CF18DD/E/827/ECO.....	50	A	•	+	•
20724	CF18DD/E/830/ECO.....	50	A	•	+	•
20672	CF18DD/E/835/ECO.....	50	A	•	+	•
20668	CF18DD/E/841/ECO.....	50	A	•	+	•
20684	CF26DD/E/827/ECO.....	50	A	•	+	•
20722	CF26DD/E/830/ECO.....	50	A	•	+	•
20673	CF26DD/E/835/ECO.....	50	A	•	+	•
20669	CF26DD/E/841/ECO.....	50	A	•	+	•

Fluorescent Dulux

DULUX® D & D/E (Double) SuperSaver



20224	CF18DD/E/15W/SS/830/ECO.....	50	Ⓟ C	•	•
20225	CF18DD/E/15W/SS/835/ECO.....	50	Ⓟ C	•	•
20226	CF18DD/E/15W/SS/841/ECO.....	50	Ⓟ C	•	•
20457	CF26DD/E/21W/SS/830/ECO.....	50	Ⓟ C	•	•
20458	CF26DD/E/21W/SS/835/ECO.....	50	Ⓟ C	•	•
20459	CF26DD/E/21W/SS/841/ECO.....	50	Ⓟ C	•	•

Fluorescent Dulux

DULUX® EL Micromini



29160	CF5EL/MICRO/827.....	6	Ⓟ C	•	•	
29133	CF5EL/MICRO/827/C.....	6	Ⓟ C	•	•	
Value Added Product						
29734	☀️ CF13EL/MICRO/827/C/RP2.....	12	Ⓟ C	•	+	•
29727	CF13EL/MICRO/827/RP2.....	12	Ⓟ C	•	•	•
29898	CF13EL/MICRO/830/ECO.....	6	Ⓟ C	•	+	•
29728	CF20EL/MICRO/827/RP2.....	12	Ⓟ C	•	•	•
29899	CF20EL/MICRO/830/ECO.....	6	Ⓟ C	•	+	•
29729	CF23EL/MICRO/827/RP2.....	12	Ⓟ C	•	•	•
29901	CF23EL/MICRO/830/ECO.....	6	Ⓟ C	•	+	•
29026	CF26EL/MICRO/827/ECO.....	6	Ⓟ C	•	•	•
28990	CF26EL/MICRO/830/ECO.....	6	Ⓟ C	•	•	•

Fluorescent Dulux

DULUX® EL Living Spaces™



21094	☀️ CF5EL/MICRO/827/C/LS.....	6	Ⓟ C	•	•	
21095	CF5EL/MICRO/LS.....	6	Ⓟ C	•	•	
Value Added Product						
27718	☀️ CF10EL/MICRO/827/LS/RP2.....	12	Ⓟ C	•	•	
29976	☀️ CF13EL/MICRO/827/LS/RP2/WING4	48	Ⓟ C	•	•	
29972	CF13EL/MICROMINI/827/LS/RP2...	12	Ⓟ C	•	•	
27716	☀️ CF13EL/MICROC/827/LS/RP2.....	12	Ⓟ C	•	•	
29973	CF20EL/MICRO/827/LS/RP2.....	12	Ⓟ C	•	•	
29974	CF23EL/MICRO/827/LS/RP2.....	12	Ⓟ C	•	+	•
29023	CF26EL/MICRO/827/LS.....	6	Ⓟ C	•	•	•
28974	CF33EL/3WAY/LS/827/BL.....	4	Ⓟ C	•	•	•

SYLVANIA EXCLUDED LARGE LAMP PRODUCTS

Effective May 1, 2012

VENDOR ID. NO. DCI 046135 UPC 46135	ORDERING ABBREVIATION	STD CASE QTY	S T K	DIST STOCK COST	SUGG USER PRICE
OS Item No.					

LUMALUX Plus®

67660	LU310/PLUS/ECO.....	20	A	132.90	196.82
67312	LU400/PLUS/ECO.....	20	A	78.78 +	116.68
67316	LU1000/PLUS/ECO.....	6	A	250.08	370.37

Sodium - HPS

PLANTASTAR® - For Plant Growth



67314	LU1000/PLANTASTAR.....	6	C	362.02	666.11
-------	------------------------	---	---	--------	--------

Sodium - LPS


Low Pressure Sodium



69510	SOX18.....	12	C	131.70	242.33
69511	SOX35 PLUS.....	12	C	145.83	268.33
69512	SOX55.....	12	C	146.90	270.30
69513	SOX90 PLUS.....	12	C	170.40	313.54
69514	SOX135 PLUS.....	12	C	237.76	437.48
Value Added Product					
69519	SOX180 6PK.....	6	C	238.91	439.59

Fluorescent Dulux


DULUX® S (Single)



21279	CF5DS/827/ECO.....	50	C	8.01	14.74
21278	CF5DS/841/ECO.....	50	C	8.01	14.74
21277	CF7DS/827/ECO.....	50	A	7.98	11.82
21276	CF7DS/835/ECO.....	50	A	7.98	11.82
21274	CF7DS/841/ECO.....	50	A	7.98	11.82
21275	CF7DS/850/ECO.....	50	A	8.66	12.83
21272	CF9DS/827/ECO.....	50	A	7.98	11.82
21273	CF9DS/835/ECO.....	50	A	7.98	11.82
21270	CF9DS/841/ECO.....	50	A	7.98	11.82
21271	CF9DS/850/ECO.....	50	A	8.66	12.83
Value Added Product					
20534	CF13DS/827/CVP.....	10	C	8.95	16.47
21136	CF13DS/827/ECO.....	50	A	7.35	10.89
21133	CF13DS/830/ECO.....	50	A	7.35	10.89
21137	CF13DS/835/ECO.....	50	A	7.35	10.89
21134	CF13DS/841/ECO.....	50	A	7.35	10.89
21135	CF13DS/850/ECO.....	50	A	8.76	12.97
21251	DULUX S 9W/78.....	50	C	9.82	18.07

Fluorescent Dulux

DULUX® S/E (Single)




20315	CF5DS/E/841.....	50	C	10.21	18.79
20312	CF7DS/E/827.....	50	C	10.21	18.79
20316	CF7DS/E/841.....	50	C	10.21	18.79
20313	CF9DS/E/827.....	50	C	10.21	18.79
20317	CF9DS/E/841.....	50	C	10.21	18.79
20314	CF13DS/E/827.....	50	C	10.21	18.79
20284	CF13DS/E/830.....	50	C	10.21	18.79
20318	CF13DS/E/841.....	50	C	10.21	18.79

VENDOR ID. NO. DCI 046135 UPC 46135	ORDERING ABBREVIATION	STD CASE QTY	S T K	DIST STOCK COST	SUGG USER PRICE
OS Item No.					

Fluorescent Dulux

DULUX® D (Double)



21122	CF9DD827/ECO.....	50	C	16.72	30.76
21097	CF9DD/827/RP/ECO.....	10	C	16.72	30.76
21121	CF9DD/830/ECO.....	50	C	16.72	30.76
21123	CF9DD/835/ECO.....	50	C	16.72	30.76
21117	CF13DD/827/ECO.....	50	C	14.74	27.12
21119	CF13DD/830/ECO.....	50	C	14.74	27.12
21118	CF13DD/835/ECO.....	50	C	14.74	27.12
21120	CF13DD/841/ECO.....	50	C	14.74	27.12
21109	CF18DD/827/ECO.....	50	C	19.88	36.58
21112	CF18DD/830/ECO.....	50	C	19.88	36.58
21110	CF18DD/835/ECO.....	50	C	19.88	36.58
21111	CF18DD/841/ECO.....	50	C	19.88	36.58
21113	CF26DD/827/ECO.....	50	C	20.00	36.80
21116	CF26DD/830/ECO.....	50	C	20.00	36.80
21114	CF26DD/835/ECO.....	50	C	20.00	36.80
21115	CF26DD/841/ECO.....	50	C	20.00	36.80

Fluorescent Dulux

DULUX® D/E (Double)



20682	CF13DD/E/827/ECO.....	50	C	17.09 +	31.45
20721	CF13DD/E/830/ECO.....	50	C	17.09 +	31.45
20671	CF13DD/E/835/ECO.....	50	C	17.09 +	31.45
20667	CF13DD/E/841/ECO.....	50	C	17.09 +	31.45
20683	CF18DD/E/827/ECO.....	50	A	21.75 +	32.21
20724	CF18DD/E/830/ECO.....	50	A	21.75 +	32.21
20672	CF18DD/E/835/ECO.....	50	A	21.75 +	32.21
20668	CF18DD/E/841/ECO.....	50	A	21.75 +	32.21
20684	CF26DD/E/827/ECO.....	50	A	21.75 +	32.21
20722	CF26DD/E/830/ECO.....	50	A	21.75 +	32.21
20673	CF26DD/E/835/ECO.....	50	A	21.75 +	32.21
20669	CF26DD/E/841/ECO.....	50	A	21.75 +	32.21

Fluorescent Dulux

DULUX® D & D/E (Double) SuperSaver



20224	CF18DD/E/15W/SS/830/ECO.....	50	C	33.41	61.47
20225	CF18DD/E/15W/SS/835/ECO.....	50	C	33.41	61.47
20226	CF18DD/E/15W/SS/841/ECO.....	50	C	33.41	61.47
20457	CF26DD/E/21W/SS/830/ECO.....	50	C	33.41	61.47
20458	CF26DD/E/21W/SS/835/ECO.....	50	C	33.41	61.47
20459	CF26DD/E/21W/SS/841/ECO.....	50	C	33.41	61.47

Fluorescent Dulux

DULUX® EL Micromini



29160	CF5EL/MICRO/827.....	6	C	6.04	11.11
29133	CF5EL/MICRO/827/C.....	6	C	5.86	10.78
Value Added Product					
29734	CF13EL/MICRO/827/C/RP2.....	12	C	21.95 +	40.39
29727	CF13EL/MICRO/827/RP2.....	12	C	21.95	40.39
29898	CF13EL/MICRO/830/ECO.....	6	C	21.95 +	40.39
29728	CF20EL/MICRO/827/RP2.....	12	C	21.14	38.90
29899	CF20EL/MICRO/830/ECO.....	6	C	18.42 +	33.89