



T6.5



A19



R14 Inter



R14



T8



T10

## GENERAL PURPOSE LAMPS

Watts	Bulb	Base	Product Number	Symbols & Footnotes	Ordering Abbreviation	Volts	Pkg Qty	Description	Class & Filament	Avg Rated Life (hrs)	Lumens Beam Angle CBCP	LCL (in)	MOL (in)	
20	T6.5	DC Bayonet	18144	1	<b>20T6.5DC/IF</b>	120	60	Inside Frost Exit Lamp	B, C-8	10000	92		5.56	
			18143	1	<b>20T6.5/IF</b>	120	60	Inside Frost Exit Lamp	B, C-8	10000	92		5.50	
25	A19	Med	11090	●	<b>25A/RS</b>	120	120	Inside Frost Rough Service	B, C-17	1000	210	2.50	3.94	
			11092	●	<b>25A/RS</b>	130	120	Inside Frost Rough Service	B, C-17	1000	210	2.50	3.94	
			10562	●	<b>25A/W/RP</b>	120	24	Soft White	C, C-9	2500	160	2.50	3.94	
			10644	●	<b>25A</b>	120	120	Standard Frost	B, C-9	2500	190	2.50	3.94	
			10634	●	<b>25A/RP</b>	120	24	Standard Frost	B, C-9	2500	190	2.50	3.94	
			10645	● <sup>136,146</sup>	<b>25A</b> <i>@120_volts, approximate 22 watts, 130 lumens, 6250 hours</i>	130	120	Standard Frost	B, C-9	2500	180	2.50	3.94	
			11285	●	<b>25A</b>	230	120	Standard Frost	B, C-17	1000	205	2.50	3.94	
			11289	●	<b>25A</b>	277	120	Standard Frost	B, C-17	1000	187	2.50	3.94	
			Med Brass	10693		<b>25A/CL</b>	120	120	Clear	B, C-9	2500	190	2.50	3.94
				10683		<b>25A/CL/RP</b>	120	24	Clear	B, C-9	2500	190	2.50	3.94
				10694	<sup>136,146</sup>	<b>25A/CL</b> <i>@120_volts, approximate 22 watts, 130 lumens, 6250 hours</i>	130	120	Clear	B, C-9	2500	180	2.50	3.94
				11710		<b>25A19/TB/RP</b>	125	6	Transparent Blue	B, C-9	3000		2.50	3.94
				11714		<b>25A19/TG/RP</b>	125	6	Transparent Green	B, C-9	3000		2.50	3.94
				11711		<b>25A19/TO/RP</b>	125	6	Transparent Orange	B, C-9	3000		2.50	3.94
				11712		<b>25A19/TR/RP</b>	125	6	Transparent Red	B, C-9	3000		2.50	3.94
11713		<b>25A19/TY/RP</b>		125	6	Transparent Yellow	B, C-9	3000		2.50	3.94			
10449		<b>25A</b>		12	120	Standard Frost	B, C-6	1000	385	2.50	3.94			
R14	Intermediate	14793		●	<b>25R14N</b>	120	60	Reflector Mini Flood	B, CC-2V	1500	132		2.56	
		14784	●	<b>25R14N/RP</b>	120	6	Reflector Mini Flood	B, CC-2V	1500	132		2.56		
	Med	14818	●	<b>25R14/RP</b>	120	6	Reflector Mini Flood	C, CC-2V	1500	132		2.25		
T6.5	DC Bayonet	18129		<b>25T6.5/DC</b>	120	60	Clear Scale Illuminator	B, C-8	1000	242		5.56		
		18106		<b>25T6.5/DC</b>	130	60	Clear Scale Illuminator	B, C-8	1000	242		5.56		
		18117		<b>25T6.5/DC/IF</b>	120	60	Inside Frost Scale Illuminator	B, C-8	1000	225		5.56		
	Intermediate	18125		<b>25T6.5</b>	120	60	Clear	B, C-8	1000	242		5.50		
		18496		<b>25T6.5/CL/BL/10PK</b>	120	10	Clear	B, C-8	1000	242		5.50		
		18495		<b>25T6.5/BL/6PK</b>	120	6	Clear	B, C-8	1000	242		5.50		
		18128		<b>25T6.5</b>	130	60	Clear	B, C-8	1000	242		5.50		
		18113		<b>25T6.5/IF</b>	120	60	Inside Frost	B, C-8	1000	225		5.50		
18111		<b>25T6.5/IF</b>	130	60	Inside Frost	B, C-8	1000	225		5.50				
T8	Candelabra	18289	●111	<b>25T8C</b>	120	60	Clear Home Appliance	B, C-7A	1000	230	1.50	2.63		
		DC Bayonet	18310	111	<b>25T8DC</b>	120	60	Clear Home Appliance	B, C-7A	1000	230	1.31	2.63	
	Intermediate	18321	111	<b>25T8DC/BL</b>	120	12	Clear Home Appliance	B, C-7A	1000	230	1.31	2.63		
		18316	111	<b>25T8DC</b>	130	60	Clear Home Appliance	B, C-7A	1000	215	1.31	2.63		
		18359	111	<b>25T8N</b>	120	60	Clear Home Appliance	B, C-7A	1000	230	1.31	2.63		
	18365	111	<b>25T8N/BL</b>	120	12	Clear Home Appliance	B, C-7A	1000	230	1.31	2.63			
	18360	111	<b>25T8N/BL/1/6</b>	120	6	Clear Home Appliance	B, C-7A	1000	230	1.31	2.63			
T10	Med	18510	●	<b>25T10</b>	120	60	Clear	B, C-8	1000	232		5.63		