

Item Number	OSRAM SYLVANIA Description	Input Voltage (VAC)	Circuit Type	Input Power (Watts)	Advance Catalog # ⁸	Universal Lighting Technologies* Catalog # ⁸	Venture Lighting Catalog # ⁸	Howard Industries Catalog # ^{8,9}
310W High Pressure Sodium Lamp - ANSI Code S67								
47643	LU310/MULTI-KIT	120/208/ 240/277	CWA	355	71A8391 & 71A8371-001D	---	V90D1810K	---
47644	LU310/480-KIT	480	CWA	355	71A8341	---	---	---
400W High Pressure Sodium Lamp - ANSI Code S51								
47647	LU400/SUPER5-KIT	120/208/ 240/277/480	CWA	464	71A8453 & 71A8453-001D	S400ML5AC4M & S400ML5AC4M-500K	---	---
47364	LU400/MULTI-KIT	120/208/ 240/277	CWA	464	71A8493 & 71A8473-001D	S400MLTAC4M & S400MLTAC4M-500K	V90D1911K & V90D1912K	S040071C211
47376	LU400/480-KIT	480	CWA	464	71A8443 & 71A8443-001D	---	---	S040011C211
47657	LU400/480/120T-KIT	480/120TAP	CWA	464	71A8443T	S40048TAC4M & S40048TAC4M-500K	---	---
47656	LU400/120/277-KIT	120/277	CWA	464	---	---	---	---
750W High Pressure Sodium Lamp - ANSI Code S111								
47712	LU750/MULTI-KIT	120/208/ 240/277	CWA	830	71A86E5 ^{6,7}	---	---	---
47658	LU750/480-KIT	480	CWA	830	---	---	---	---
1000W High Pressure Sodium Lamp - ANSI Code S52								
47659	LU1000/SUPER5-KIT	120/208/ 240/277/480	CWA	1100	71A8753 ⁶ & 71A8753-001 ⁶	S1000ML5AC5M & S1000ML5AC5M-500K	---	---
47389	LU1000/MULTI-KIT	120/208/ 240/277	CWA	1100	71A8793 ⁶ & 71A8773-001 ⁶	S1000MLTAC5M & S1000MLTAC5M-500K	V90D2311K	S100071C211
47391	LU1000/480-KIT	480	CWA	1100	71A8743 ⁶ & 71A8743-001 ⁶	---	---	S100011C211
METALARC® METAL HALIDE F-CAN HID BALLASTS								
175W Metal Halide Lamp - ANSI Code M57								
47743	M175/120/277/F-CAN	120/277	CWA	205	72C5581-NP & 72C5581-NP-001	1110-245SC-TC	---	---
250W Metal Halide Lamp - ANSI Code M58								
47751	M250/120/277/F-CAN	120/277	CWA	295	72C5782-NP & 72C5782-NP-001	1110-246C-TC ⁴	---	---
400W Metal Halide Lamp or 360W Metal Halide Lamp¹⁰ - ANSI Code M59								
47759	M400/120/277/F-CAN	120/277	CWA	460	72C6082-NP & 72C6082-NP-001	1110-247SC-TC	---	---
METALARC METAL HALIDE PULSE START F-CAN HID BALLASTS								
35W Metal Halide Pulse Start Lamp - ANSI Code M130								
47680	M35/120/277/F-CAN	120/277	HX-HPF	54	72C5081-NP	---	---	---
50W Metal Halide Pulse Start Lamp - ANSI Code M110								
47195	M50/120/277/F-CAN	120/277	HX-HPF	67	72C5181-NP & 72C5181-NP-001	11210-236C-TC	---	---
70W Metal Halide Pulse Start Lamp - ANSI Code M139								
47693	M70/120/277/F-CAN	120/277	HX-HPF	95	72C5281-NP	---	---	---
70W Metal Halide Pulse Start Lamp - ANSI Code M98 or M143								
47694	M70/120/277/F-CAN	120/277	HX-HPF	94	72C5282-NP & 72C5282-NP-001	11210-506C-TC	---	---
100W Metal Halide Pulse Start Lamp - ANSI Code M90								
47734	M100/120/277/F-CAN	120/277	HX-HPF	125	72C5381-NP & 72C5381-NP-001	11210-239C-TC	---	---
150W Metal Halide Pulse Start Lamp - ANSI Code M102 or M142								
47738	M150-PS/120/277/F-CAN	120/277	CWA	185	---	---	---	---
175W Metal Halide Pulse Start Lamp - ANSI Code M137 or M152								
47741	M175-PS/120/277/F-CAN	120/277	CWA	210	72C5582-NP & 72C5582-NP-001	---	---	---
200W Metal Halide Pulse Start Lamp - ANSI Code M136								
47747	M200-PS/120/277/F-CAN	120/277	CWA	240	---	---	---	---
250W Metal Halide Pulse Start Lamp - ANSI Code M138 or M153								
47749	M250-PS/120/277/F-CAN	120/277	CWA	295	72C5783-NP & 72C5783-NP-001	---	---	---
320W Metal Halide Pulse Start Lamp - ANSI Code M132 or M154								
47753	M320-PS/120/277/F-CAN	120/277	CWA	375	72C5882-NP & 72C5882-NP-001	P320277AFXM	---	---
400W Metal Halide Pulse Start Lamp - ANSI Code M155 or M135								
47757	M400-PS/120/277/F-CAN	120/277	CWA	465	72C6182-NP & 72C6182-NP-001	---	---	---