

Specification Data

Fixture Description:	Type
Project/Job:	
SYLVANIA lamp:	
SYLVANIA ballast:	
Notes:	

Ordering Information

Item Number	Ordering Abbreviation	Watts	Nominal Length (in)	Initial Lumens	Mean Lumens ¹	Lumens per Watt	Average Rated Life				CCT	CRI
							Instant Start 3 hrs/ start	12 hrs/ start	Prog. Rapid Start 3 hrs/ start	12 hrs/ start		
OCTRON® 800 XP® SUPERSAVER®												
22405	F017/15W/830/XP/SS/EC03	15	24	1200	1130	80	24,000	40,000	40,000	42,000	3000K	85
22406	F017/15W/835/XP/SS/EC03	15	24	1200	1130	80	24,000	40,000	40,000	42,000	3500K	85
22407	F017/15W/841/XP/SS/EC03	15	24	1200	1130	80	24,000	40,000	40,000	42,000	4100K	85
22395	F025/21W/835/XP/SS/EC03	21	36	1925	1810	92	24,000	40,000	40,000	42,000	3500K	85
22396	F025/21W/841/XP/SS/EC03	21	36	1925	1810	92	24,000	40,000	40,000	42,000	4100K	85
22232	F032/25W/830/XP/SS/EC03	25	48	2500	2350	100	24,000	40,000	40,000	42,000	3000K	85
22233	F032/25W/835/XP/SS/EC03	25	48	2500	2350	100	24,000	40,000	40,000	42,000	3500K	85
22234	F032/25W/841/XP/SS/EC03	25	48	2500	2350	100	24,000	40,000	40,000	42,000	4100K	85
22235	F032/25W/850/XP/SS/EC03	25	48	2500	2350	100	24,000	40,000	40,000	42,000	5000K	81
22177	F028/830/XP/SS/EC03	28	48	2725	2560	97	24,000	40,000	40,000	42,000	3000K	85
22178	F028/835/XP/SS/EC03	28	48	2725	2560	97	24,000	40,000	40,000	42,000	3500K	85
22179	F028/841/XP/SS/EC03	28	48	2725	2560	97	24,000	40,000	40,000	42,000	4100K	85
22184	F028/850/XP/SS/EC03	28	48	2725	2560	97	24,000	40,000	40,000	42,000	5000K	81
22063	F030/830/XP/SS/EC03	30	48	2850	2680	95	24,000	40,000	40,000	42,000	3000K	85
22060	F030/835/XP/SS/EC03	30	48	2850	2680	95	24,000	40,000	40,000	42,000	3500K	85
22062	F030/841/XP/SS/EC03	30	48	2850	2680	95	24,000	40,000	40,000	42,000	4100K	85
22202	F030/850/XP/SS/EC03	30	48	2850	2680	95	24,000	40,000	40,000	42,000	5000K	81
OCTRON F096 XP SUPERSAVER												
22420	F096/50W/835/XP/SS/EC03	50	96	5400	5075	108	24,000	36,000			3500K	85
22421	F096/50W/841/XP/SS/EC03	50	96	5400	5075	108	24,000	36,000			4100K	85
22100	F096/54W/835/XP/SS/EC03	54	96	5700	5360	106	24,000	36,000			3500K	85
22101	F096/54W/841/XP/SS/EC03	54	96	5700	5360	106	24,000	36,000			4100K	85
22347	F096/54W/850/XP/SS/EC03	54	96	5700	5360	106	24,000	36,000			5000K	81

1. Measured at 40% of rated life.

Ordering Guide

FO	30	/	8	35	XP	/	SS	/	EC03
Fluorescent OCTRON	Actual Wattage 15, 21, 25, 28, 30, 50 and 54		Actual CRI 80 or 85	Color Temperature 30 = 3000K CCT, 35 = 3500K CCT 41 = 4100K CCT, 50 = 5000K CCT	XP= EX tended Performance		SUPERSAVER		ECOLOGIC3

Lamp Dimensions

Lamp Type	(A) Max. Overall Length (in.)	(B) Base Face to Opposite Pin (in.)	(C) Max. Base Face to Base Face (in.)	(D) Max. Outside Diameter (in.)
F017	23.78	Min. 23.41 Max. 23.50	23.22	1.1
F025	35.78	Min. 35.40 Max. 35.50	35.22	1.1
F032 F032/25W	47.78	Min. 47.41 Max. 47.50	47.22	1.1
F028 F030				
F096	94.00	Min. 93.42 Max. 93.65	93.30	1.1