

LED Directional Lamps



Item Number	Ordering Abbreviation	ENERGY STAR®	Wattage (W)	Lumens	Beam Angle	CBCP (cd)	Color	CRI	Lifetime (Hrs)	Replacing
PAR38										
78735	LED10PAR38/SG/830/WSP15	Yes	10	640	15°	6900	3000K	82	50,000	60W Halogen
78796	LED15PAR38/SG/830/SP10	Yes	15	760	10°	16000	3000K	89	50,000	60W Halogen
78006	LED15PAR38/830/WSP12/SG2	N/A	15	760	12°	11000	3000K	89	50,000	60W Halogen
78795*	LED15PAR38/SG/830/WSP12	Yes	15	760	12°	11000	3000K	89	50,000	60W Halogen
78719	LED15PAR38/SG/827/WSP15	Yes	15	700	15°	7000	2700K	89	50,000	60W Halogen
78498	LED15PAR38/SG/830/WSP15	Yes	15	760	15°	7500	3000K	89	50,000	60W Halogen
78436	LED16PAR38/DIM/827/FL40	Yes	16	950	40°	1680	2700K	81	25,000	75W Halogen
78658*	LED18PAR38/DIM/827/FL40	Yes	18	860	40°	1150	2700K	84	25,000	75W Halogen
78435	LED16PAR38/DIM/827/NFL25	Yes	16	950	25°	4300	2700K	81	25,000	75W Halogen
78657*	LED18PAR38/DIM/827/NFL25	Yes	18	860	25°	3680	2700K	84	25,000	75W Halogen
78433	LED16PAR38/DIM/830/NFL25	Yes	16	1000	25°	4500	3000K	82	25,000	75W Halogen
78640*	LED18PAR38/DIM/830/NFL25	Yes	18	900	25°	3100	3000K	87	50,000	75W Halogen
78434	LED16PAR38/DIM/830/FL40	Yes	16	1000	40°	1745	3000K	82	25,000	75W Halogen
78641*	LED18PAR38/DIM/830/FL40	Yes	18	900	40°	1500	3000K	87	50,000	75W Halogen
72531	LED16PAR38/DIM/850/FL40 [RP]	N/A	16	950	40°	2000	5000K	86	25,000	75W Halogen
78761*	LED18PAR38/DIM/840/FL40	Yes	18	920	40°	1620	4000K	89	50,000	75W Halogen
78904	LED20PAR38/DIM/P/927/WSP12	Yes	20	1000	12°	14000	2700K	93	40,000	90W Halogen
78906	LED20PAR38/DIM/P/930/WSP12	Yes	20	1050	12°	18000	3000K	93	40,000	90W Halogen
78207	LED20PAR38/DIM/830/FL40	N/A	20	1300	40°	2500	3000K	82	25,000	120W Halogen
78807*	LED24PAR38/DIM/830/FL40	No	24	1300	40°	2020	3000K	85	25,000	90W Halogen
78745	LED21PAR38/DIM/P/930/FL30	Yes	21	1150	30°	3700	3000K	95	50,000	90W Halogen
78741	LED21PAR38/GU24/DIM/P/930/FL30	Yes	21	1150	30°	3700	3000K	95	50,000	90W Halogen
78806*	LED24PAR38/DIM/830/NFL25	No	24	1300	25°	4930	3000K	85	25,000	90W Halogen



PAR38 High Output										
78958	LED15PAR38/SGHO/830/NFL25	Yes	15	1050	25°	5000	3000K	82	25,000	24W HID
78957	LED15PAR38/SGHO/830/SP10	Yes	15	1050	10°	26000	3000K	82	25,000	24W HID



PAR30										
78662	LED10PAR30/DIM/SG/827/SP10	Yes	10	510	10°	11000	2700K	89	50,000	50PAR30
78576	LED10PAR30/DIM/SG/827/WSP15	Yes	10	510	15°	5000	2700K	89	50,000	50PAR30
78919	LED10PAR30/DIM/SG/827/NFL20	No	10	600	20°	3000	2700K	89	25,000	50PAR30
78663	LED10PAR30/DIM/SG/827/NFL25	Yes	10	510	25°	2300	2700K	89	50,000	50PAR30
78664	LED10PAR30/DIM/SG/830/SP10	Yes	10	550	10°	12000	3000K	89	50,000	50PAR30
78665	LED10PAR30/DIM/SG/830/WSP15	Yes	10	550	15°	5400	3000K	89	50,000	50PAR30
78666	LED10PAR30/DIM/SG/830/NFL25	Yes	10	550	25°	2500	3000K	89	50,000	50PAR30
78747	LED15PAR30/DIM/P/930/FL40	Yes	15	880	40°	1700	3000K	95	50,000	60W Halogen
78743	LED15PAR30/GU24/DIM/P/930/FL40	Yes	15	880	40°	1700	3000K	95	50,000	50W Halogen



*Products being phased out

N/A = Information not available at this time
O/T = Product is currently on test

