

RAPID START LAMPS

High Output (800mA) Standard Rapid Start Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	CRI	Approx Lumens @25°C/77°F		Symbols & Footnotes
											Initial	Mean	
110	T12	96	93.91	Recessed DC	25164	F96T12/DSGN50/HO	15	12000	5000	90	6450	5225	31,33,48,97
					25185	F96T12/D865/HO	15	12000	6500	80	8800	7920	31,33,48,97

High Output (800mA) Rapid Start Lamps for Cold Temperature Operation

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	CRI	Approx Lumens @25°C/77°F		Symbols & Footnotes
											Initial	Mean	
110		96	93.91	Recessed DC	25118	F96T12/CW/HO/COLD/10/CVP	10	12000	4200	60	8600	6966	31,33,48,91,97
					25129	F96T12/CW/HO/CT/ECO	15	12000	4200	60	8600	6966	31,33,48,76,91,97
					25134	F96T12/CW/HO/COLD TEMP	15	12000	4200	60	8600	6966	31,33,48,91,97
					25135	F96T12/D/HO/COLD TEMP	15	12000	6500	76	7600	6156	31,33,48,91,97

Very High Output (1500mA) SUPERSAVER® Rapid Start Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	CRI	Approx Lumens @25°C/77°F		Symbols & Footnotes
											Initial	Mean	
195	T12	96	93.91	Recessed DC	25296	F96T12/CW/VHO/SS	15	10000	4200	60	13000	9100	28,31,33,48,108

Very High Output (1500mA) Standard Rapid Start Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	CRI	Approx Lumens @25°C/77°F		Symbols & Footnotes
											Initial	Mean	
115	T12	48	46	Recessed DC	25248	F48T12/CW/VHO	30	10000	4200	60	6600	4620	31,33,48,108
					25249	F48T12/CW/VHO/LT	30	10000	4200	60	6750	5250	31,33,48,58,88,108
					25244	F48T12/D/VHO	30	10000	6500	76	5600	3920	31,33,48,108
135	T12	60	57.91	Recessed DC	25262	F60T12/CW/VHO	30	10000	4200	60	8700	6090	31,33,48,108
141	T12	60	57.91	Recessed DC	25263	F60T12/CW/VHO/LT	30	10000	4200	60	8700	6090	31,33,48,58,88,108
160	T12	72	69.91	Recessed DC	25272	F72T12/CW/VHO	15	10000	4200	60	10600	7420	31,33,48,108
					25274	F72T12/CW/VHO/LT	15	10000	4200	60	11000	7700	31,33,48,58,88,108
					25270	F72T12/D/VHO	15	10000	6500	76	9400	6580	31,33,48,108
215	T12	96	93.91	Recessed DC	25209	F96T12/CW/VHO	15	10000	4200	60	14000	9800	31,33,48,108
					25292	F96T12/CW/VHO/LT	15	10000	4200	60	15000	10500	31,33,48,58,88,108
					25210	F96T12/D/VHO	15	10000	6500	76	11600	8120	31,33,48,108

INSTANT START LAMPS

Slimline SUPERSAVER® Instant Start Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	CRI	Approx Lumens @25°C/77°F		Symbols & Footnotes
											Initial	Mean	
32	T12	48	46.00	Single Pin	24829	F48T12/D35/SS	30	9000	3500	70	2575	2369	26,31,33
					24825	F48T12/D41/SS	30	9000	4100	70	2575	2369	26,31,33
					24823	F48T12/CW/SS	30	9000	4200	60	2450	2200	26,31,33
57	T12	96	94	Single Pin	29900	F96T12/D41/SSP/ECO	15	12000	4100	82	5600	5152	26,31,33,76,97