

**SYLVANIA CONFIDENTIAL NET PRICES**

Effective May 1, 2012

VENDOR ID. NO. DCI 046135 UPC 46135	ORDERING ABBREVIATION	STD CASE QTY	S T K	DIST STOCK COST	SUGG USER PRICE
OS Item No.					

VENDOR ID. NO. DCI 046135 UPC 46135	ORDERING ABBREVIATION	STD CASE QTY	S T K	DIST STOCK COST	SUGG USER PRICE
OS Item No.					

B10, B13, C15

13316	25B10C/DL/BL 120V.....	12	Ⓞ	C	1.85	3.41
13306	25B10C/DL/BL/4PK 120V.....	24	Ⓞ	C	2.01	3.70
<b>Value Added Product</b>						
13317	25B10C/DLF/BL 120V.....	12	Ⓞ	C	2.01	3.70
13308	25B10C/DLF/BL/4PK 120V.....	24	Ⓞ	C	2.01	3.70
13453	25B10C/F/BL/2PK 120V.....	12	Ⓞ	C	1.86	3.43
13395	25B10C/F/BL/4PK 120V.....	24	Ⓞ	C	1.86	3.43
13678	25B10C/T/BL/2PK 120V.....	12	Ⓞ	B	1.77 +	2.93
13737	32B10C/CRYSTAL/DL/BL/2PK 120V.....	12	Ⓞ	C	•	•
13440	40B10/BL/2PK 120V.....	12	Ⓞ	C	1.86	3.43
13651	40B10/BL/4PK 120V.....	24	Ⓞ	B	1.77	2.93
<b>Value Added Product</b>						
15354	40B10/DAY/2PK/BL 120V.....	12	Ⓞ	C	4.62	8.51
13321	40B10/DL/BL/2PK 120V.....	12	Ⓞ	C	2.01	3.70
13332	40B10/DL/BL/4PK 120V.....	24	Ⓞ	C	2.01	3.70
<b>Value Added Product</b>						
13322	40B10/DLF/BL/2PK 120V.....	12	Ⓞ	C	2.01	3.70
13441	40B10/F/BL/2PK 120V.....	12	Ⓞ	C	1.86	3.43
13719	40B10/T/BL/2PK 120V.....	12	Ⓞ	C	1.86	3.43
13571	40B10C/BAGPK 120V.....	200	Ⓞ	B	• +	•
13456	40B10C/BL/2PK 120V.....	12	Ⓞ	C	1.69 +	3.11
13648	40B10C/BL/4PK 120V.....	24	Ⓞ	B	1.77	2.93
13741	40B10C/CRYSTAL/DL/BL/2PK 120V.....	12	Ⓞ	B	•	•
13714	40B10C/CRYSTAL/DL/BL/4/24 120V.....	24	Ⓞ	B	•	•
<b>Value Added Product</b>						
13751	40B10C/DAY/2PK/BL 120V.....	12	Ⓞ	C	4.62	8.51
13319	40B10C/DL/BL/2PK 120V.....	12	Ⓞ	C	1.85	3.41
13328	40B10C/DL/BL/4PK 120V.....	24	Ⓞ	C	2.01	3.70
<b>Value Added Product</b>						
13320	40B10C/DLF/BL/2PK 120V.....	12	Ⓞ	C	2.01	3.70
13309	40B10C/DLF/BL/4PK 120V.....	24	Ⓞ	C	2.01	3.70
13457	40B10C/F/BL/2PK 120V.....	12	Ⓞ	C	1.86	3.43
13396	40B10C/F/BL/4PK 120V.....	24	Ⓞ	C	1.86	3.43
13681	40B10C/T/BL/2PK 120V.....	12	Ⓞ	B	1.77 +	2.93
13785	40B13/CRYSTAL/FAN/BL/2PK 120V.....	12	Ⓞ	C	•	•
13369	40B13/DL/FAN/BL/2PK 120V.....	12	Ⓞ	C	3.49	6.42
13367	40B13/FAN/BL/2PK 120V.....	12	Ⓞ	C	2.89	5.32
13357	40B13C/CL/FAN/2/12/BL 120V.....	12	Ⓞ	C	2.89	5.32
13442	60B10/BL/2PK 120V.....	12	Ⓞ	C	1.86	3.43
13650	60B10/BL/4PK 120V.....	24	Ⓞ	B	1.77	2.93
13323	60B10/DL/BL/2PK 120V.....	12	Ⓞ	C	2.01	3.70
13254	60B10/DL/BL/4PK 120V.....	24	Ⓞ	C	1.85	3.41
<b>Value Added Product</b>						
13324	60B10/DLF/BL/2PK 120V.....	12	Ⓞ	C	2.01	3.70
13443	60B10/F/BL/2PK 120V.....	12	Ⓞ	C	1.86	3.43
13721	60B10/T/BL/2PK 120V.....	12	Ⓞ	C	1.86	3.43
13572	60B10C/BAGPK 120V.....	200	Ⓞ	B	• +	•
13460	60B10C/BL/2PK 120V.....	12	Ⓞ	C	1.86 +	3.43
13649	60B10C/BL/4PK 120V.....	24	Ⓞ	B	1.77	2.93
<b>Value Added Product</b>						
13750	60B10C/DAY/2PK/BL 120V.....	12	Ⓞ	C	4.24	7.80
13777	60B10C/DL/BL/2PK 120V.....	12	Ⓞ	C	2.01	3.70
13778	60B10C/DLF/BL/2PK 120V.....	12	Ⓞ	C	2.01	3.70
13705	60B10C/DL/BL/4PK 120V.....	24	Ⓞ	C	2.01	3.70
13754	60B10C/DLF/BL/4PK 120V.....	24	Ⓞ	C	2.01	3.70
13461	60B10C/F/BL/2PK 120V.....	12	Ⓞ	C	1.86	3.43
13399	60B10C/F/BL/4PK 120V.....	24	Ⓞ	C	1.86	3.43
13684	60B10C/T/BL/2PK 120V.....	12	Ⓞ	C	1.86	3.43
13370	60B13/DL/FAN/BL/2PK 120V.....	12	Ⓞ	C	3.49	6.42
13368	60B13/FAN/BL/2PK 120V.....	12	Ⓞ	C	2.89	5.32
13263	60B13C/CL/FAN/2/12/BL 120V.....	12	Ⓞ	C	2.89	5.32

**Décor**

Globe



13616	15G16.5C 120V.....	24	Ⓞ	B	2.11 +	3.50
13709	15G16.5C/4M 120V.....	24(6)	Ⓞ	C	2.56	4.71
10298	25G16.5/BL 120V.....	12	Ⓞ	C	2.21	4.08
10297	25G16.5/W/BL 120V.....	12	Ⓞ	C	2.21	4.08
13618	25G16.5C 120V.....	24	Ⓞ	B	2.11 +	3.50
13704	25G16.5C/4M 120V.....	24	Ⓞ	C	2.56	4.71
13625	25G16.5C/BL 120V.....	12	Ⓞ	C	2.21	4.08
10221	25G16.5C/DAY/2PK/BL 120V.....	12	Ⓞ	C	5.51	10.14
13622	25G16.5C/W/BL 120V.....	12	Ⓞ	B	2.11 +	3.50
14264	25G25 120V.....	24	Ⓞ	B	3.72 +	6.18
14145	25G25/DL/RP 120V.....	6	Ⓞ	C	5.42	9.98
14276	25G25/4M 120V.....	24	Ⓞ	C	4.09	7.52
14146	25G25/DLSW/RP 120V.....	6	Ⓞ	C	5.42	9.98
14282	25G25/RP 120V.....	6	Ⓞ	C	3.87	7.13
14265	25G25/W 120V.....	24	Ⓞ	B	3.72 +	6.18
14286	25G25/W/RP 120V.....	6	Ⓞ	C	3.87	7.13
14685	25G40 120V.....	6	Ⓞ	C	8.83	16.24
10300	40G16.5/BL 120V.....	12	Ⓞ	C	2.21	4.08
10299	40G16.5/W/BL 120V.....	12	Ⓞ	C	2.21	4.08
13702	40G16.5C 120V.....	24	Ⓞ	C	2.21 +	4.08
13666	40G16.5C/BL 120V.....	12	Ⓞ	C	2.21	4.08
13667	40G16.5C/W/BL 120V.....	12	Ⓞ	C	2.21 +	4.08
14266	40G25 120V.....	24	Ⓞ	A	3.01 +	4.45
14191	40G25/CVP/130V.....	6	Ⓞ	C	3.87 +	7.13
<b>Value Added Product</b>						
13966	40G25/DAY/1/6 120V.....	6	Ⓞ	C	4.83	8.88
14147	40G25/DL/RP 120V.....	6	Ⓞ	C	5.42	9.98
<b>Value Added Product</b>						
14148	40G25/DLSW/RP 120V.....	6	Ⓞ	C	5.42	9.98
14283	40G25/RP 120V.....	6	Ⓞ	C	3.87 +	7.13
14267	40G25/W 120V.....	24	Ⓞ	B	3.33 +	5.52
14190	40G25/W/CVP130V.....	6	Ⓞ	C	3.87 +	7.13
14287	40G25/W/RP 120V.....	6	Ⓞ	C	3.87	7.13
14619	40G40/RP 120V.....	6	Ⓞ	C	8.83	16.24
14620	40G40/W/RP 120V.....	6	Ⓞ	C	8.83	16.24
10302	60G16.5/BL 120V.....	12	Ⓞ	C	2.21	4.08
10301	60G16.5/W/BL/2PK 120V.....	12	Ⓞ	C	2.21	4.08
13665	60G16.5C/BL 120V.....	12	Ⓞ	C	2.21	4.08
13664	60G16.5C/W/BL 120V.....	12	Ⓞ	C	2.21	4.08
14280	60G25 120V.....	24	Ⓞ	C	3.87	7.13
<b>Value Added Product</b>						
13967	60G25/DAY/1/6 120V.....	6	Ⓞ	C	4.83	8.88
14149	60G25/DL/RP 120V.....	6	Ⓞ	B	5.25	8.72
14150	60G25/DLSW/RP 120V.....	6	Ⓞ	C	5.42	9.98
14261	60G25/RP 120V.....	6	Ⓞ	C	3.87	7.13
14262	60G25/W/RP 120V.....	6	Ⓞ	C	3.87	7.13
14406	60G30/W/RP 120V.....	6	Ⓞ	C	6.45	11.87
14621	60G40/RP 120V.....	6	Ⓞ	C	8.83	16.24
15792	60G40/W/3/RP 120V.....	3	Ⓞ	C	8.09	14.88
15794	100G40/3/RP 120V.....	3	Ⓞ	C	8.09	14.88
15793	100G40/W/3/RP 120V.....	3	Ⓞ	C	8.09	14.88

**Décor**

Flame



13821	25F/IC/BL/2PK 120V.....	12	Ⓞ	C	2.77	5.10
13823	25F/AIC/BL/2PK 120V.....	12	Ⓞ	C	2.77	5.10