



T12 Med Bipin

T8 Med Bipin

T12 RDC

T5 Mini Bipin

CFL 2Pin

CFL 4 Pin

## SPECIALTY FLUORESCENT LAMPS

### Diazo (SDB)

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	Approx Lumens @25°C/77°F		Symbols & Footnotes
										Initial	Mean	
65	T12	48	47.78	Med Bipin	24465	F40T12/SDB/65W	30	1000				115

### Blacklight, Preheat Lamps (Starter Required)

These lamps are not intended and should not be used for diagnostic, therapeutic or cosmetic purposes.

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	Approx Lumens @25°C/77°F		Symbols & Footnotes
										Initial	Mean	
15	T8	18	17.78	Med Bipin	21623	F15T8/350BL	24	7500				31,33,59,60,105
20	T12	24	23.78	Med Bipin	22113	F20T12/350BL	24	9000				31,33,59,60,105
22	T12	15	14.78	Med Bipin	21445	F15T12/350BL/500/PH	30					31,33,59,60,111
25	T8	18	17.78	Med Bipin	21703	F25T8/350BL/18in	24	7500				31,33,59,60,107
30	T8	36	35.78	Med Bipin	23113	F30T8/350BL	24	7500				31,33,59,60,109
32	T12	18	17.78	Med Bipin	21525	F18T12/350BL/700/PH	30					31,33,59,60,112

### Blacklight, Rapid Start Lamps (No Starter Required)

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	Approx Lumens @25°C/77°F		Symbols & Footnotes
										Initial	Mean	
40	T12	48	47.78	Med Bipin	24922	F40/350BL	30	20000				2,30,31,33,56,60,64,110
115	T12	48	45.91	Recessed DC	25251	FR48T12/350BL/VHO/180	30	10000				31,33,60,90,113

### Blacklight Blue, Preheat Lamps (Starter Required)

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	Approx Lumens @25°C/77°F		Symbols & Footnotes
										Initial	Mean	
4	T5	6	5.91	Mini Bipin	20425	F4T5/BLB	24	6000				31,33,59,60,99
8	T5	12	11.91	Mini Bipin	20825	F8T5/BLB	24	7500				31,33,59,60,99
15	T8	18	17.78	Med Bipin	21625	F15T8/BLB	6	7500				31,33,59,60,99

### Blacklight Blue, Rapid Start Lamps (No Starter Required)

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	Approx Lumens @25°C/77°F		Symbols & Footnotes
										Initial	Mean	
40	T12	48	47.78	Med Bipin	24026	F40/BLB/RP	6	20000				2,30,31,33,56,60,64,102

## GERMICIDAL LAMPS

### Germicidal Compact Fluorescent Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	Approx Lumens @25°C/77°F		Symbols & Footnotes
										Initial	Mean	
7	T5			G23	23372	GCF7DS/G23/SE/OF	10	8000				31,33,45,47,50,82
9	T5			G23	23373	GCF9DS/G23/SE/OF	10	8000				31,33,45,47,50,82
11	T4			G23	23377	GCF11DS/G23/SE/OF	10	8000				31,33,45,47,50,82
18	T5			2G11	23378	GFT18DL/2G11/SE/OF	10	8000				31,33,36,48,74,82
24	T5			2G11	23379	GFT24DL/2G11/SE/OF	10	8000				31,33,36,48,74,82