




Circline 4-Pin T5



T12 Med Bipin

## PENTRON® T5 FLUORESCENT LAMPS

### PENTRON® Circline T5 Lamps

Nominal Wattage	Bulb	Outside Diameter (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start (@12hrs/start)	CCT (K)	CRI	Approx Lumens @25°C/77°F		Symbols & Footnotes
										Initial	Mean	
22	T5	8.66 - 9.06	2GX13	20702	<b>FPC22/830</b>	12	12000	3000	82	1800	1585	31,33,38,48,74
				20712	<b>FPC22/835</b>	12	12000	3500	82	1800	1585	31,33,38,48,74
				20715	<b>FPC22/841</b>	12	12000	4100	82	1800	1585	31,33,38,48,74
40	T5	11.54 - 12.01	2GX13	20731	<b>FPC40/830</b>	12	12000	3000	82	3200	2815	31,33,38,48,74
				20732	<b>FPC40/835</b>	12	12000	3500	82	3200	2815	31,33,38,48,74
				20733	<b>FPC40/841</b>	12	12000	4100	82	3200	2815	31,33,38,48,74
55	T5	11.54 - 12.01	2GX13	20741	<b>FPC55/830/HO</b>	12	12000	3000	82	4000	3520	31,33,38,48,74
				20750	<b>FPC55/835/HO</b>	12	12000	3500	82	4000	3520	31,33,38,48,74
				20751	<b>FPC55/841/HO</b>	12	12000	4100	82	4000	3520	31,33,38,48,74

### RAPID START LAMPS

Rapid Start lamps, 3-foot and 4-foot in length, are typically designated by their wattage: e.g. F40 = Fluorescent 40W. Therefore lamps previously designated as F30T12/RS/SS, F40/SS and FB40/SS energy saving types will now be designated as F25T12/RS/SS, F34/SS and FB34/SS, respectively to comply with standard lamp designation nomenclature for these families of lamps.

### 3' SUPERSAVER® Rapid Start Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	CRI	Approx Lumens @25°C/77°F		Symbols & Footnotes
											Initial	Mean	
25	T12	36	35.78	Med Bipin	23473	<b>F25T12/WW/RS/SS</b> <i>formerly F30T12/WW/RS/SS</i>	30	18000	3000	52	1975	1679	22,31,33
					23485	<b>F25T12/D35/RS/SS</b> <i>formerly F30T12/D35/RS/SS</i>	30	18000	3500	70	2050	1804	22,31,33
					23472	<b>F25T12/CW/RS/SS</b> <i>formerly F30T12/CW/RS/SS</i>	30	18000	4200	60	1925	1636	22,31,33

### 3' Standard Rapid Start Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	CRI	Approx Lumens @25°C/77°F		Symbols & Footnotes
											Initial	Mean	
30	T12	36	35.78	Med Bipin	23490	<b>F30T12/SW/RP</b>	6	18000	3000	52	2275	1934	30,31,33,48
					23482	<b>F30T12/WW/RS</b>	30	18000	3000	52	2275	1934	30,31,33,48
					23474	<b>F30T12/D830/RS</b>	30	18000	3000	80	2290	2061	30,31,33,48
					23484	<b>F30T12/D35/RS</b>	30	18000	3500	70	2250	1980	30,31,33,48
					23139	<b>F30T12/D835/RS</b>	30	18000	3500	80	2290	2061	30,31,33,48
					23493	<b>F30T12/CW/RP</b>	6	18000	4200	60	2200	1870	30,31,33,48
					23476	<b>F30T12/CW/RS</b>	30	18000	4200	60	2200	1870	30,31,33,48
					23487	<b>F30T12/CW/RS/UPC</b>	30	18000	4200	60	2200	1870	30,31,33,48
					23478	<b>F30T12/D/RS</b>	30	18000	6500	76	1900	1615	30,31,33,48

### 4' SUPERSAVER® Rapid Start Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	CRI	Approx Lumens @25°C/77°F		Symbols & Footnotes
											Initial	Mean	
34	T12	48	47.78	Med Bipin	24538	<b>F34WW/SS/ECO</b> <i>formerly F40WW/SS/ECO</i>	30	20000	3000	52	2750	2365	2,24,30,31,33,56,76
					24535	<b>F34/D30/SS/ECO</b> <i>formerly F40/D30/SS/ECO</i>	30	20000	3000	70	2800	2520	2,24,30,31,33,56,76