



DOUBLE LIFE LAMPS

Lasts 2X longer than ordinary Soft White lamps

Watts	Bulb	Base	Product Number	Symbols & Footnotes	Ordering Abbreviation	Volts	Pkg Qty	Description	Class & Filament	Avg Rated Life(hrs)	Lumens Beam Angle CBCP	LCL (in)	MOL (in)	
40	A15	Med	10046	●	40A15/CL/DL/FAN	120	24	Clear Double Life Fan Light	C, C-9	2000	350	2.38	3.50	
			10133	●	40A15/CL/DL/BL	120	12	Clear Double Life Appliance	C, C-9	2000	350	2.38	3.50	
			11664	●	40A15/DL/SW/BL/2/24	120	24	Soft White Double Life Fan	C, C-9	2000	310	2.38	3.50	
A19	Med	11646	●☀	40A/CL/DL/2PK/RP	120	24	Clear Double Life	C, CC-8	3000	385	3.13	4.44		
		10939	●☀	40A/DL/SW/4PK/RP	120	48	Soft White Double Life	C, CC-8	3000	390	3.13	4.44		
		11645	●☀	40A/DL/SW/2PK/RP	120	24	Soft White Double Life	C, CC-8	3000	390	3.13	4.44		
B10	Candelabra	13328	●▼☀	40B10C/DL/BL/4PK	120	24	Clear Double Life Décor Bent Tip	C, C-7A	3000				3.88	
		13319	●▼☀	40B10C/DL/BL/2PK	120	12	Clear Double Life Décor Bent Tip	C, C-7A	3000				3.88	
		13714	●▼☀	40B10C/CRYSTAL/DL/BL/4/24	120	24	Double Life Crystal Bent Tip	C, C-7A	3000				3.88	
		13741	●▼☀	40B10C/CRYSTAL/DL/BL/2PK	120	12	Double Life Crystal Bent Tip	C, C-7A	3000				3.88	
		13309	●▼☀	40B10C/DL/F/BL/4PK	120	24	Frosted Double Life Décor Bent Tip	C, C-7A	3000				3.88	
		13320	●▼☀	40B10C/DL/F/BL/2PK	120	12	Frosted Double Life Décor Bent Tip	C, C-7A	3000				3.88	
		Med	13321	●▼☀ ⁹⁴	40B10/DL/BL/2PK	120	12	Clear Double Life Décor Bent Tip	C, C-7A	3000				3.81
		13723	●▼☀ ⁹⁴	40B10/CRYSTAL/DL/BL/4PK	120	24	Double Life Crystal Bent Tip	C, C-7A	3000				3.81	
		13740	●▼☀ ⁹⁴	40B10/CRYSTAL/DL/BL/2PK	120	12	Double Life Crystal Bent Tip	C, C-7A	3000				3.81	
		13322	●▼☀ ⁹⁴	40B10/DL/F/BL/2PK	120	12	Frosted Double Life Décor Bent Tip	C, C-7A	3000				3.81	
B13	Med	13366	●☀	40B13/DL/FAN/2/60/BL	120	60	Clear Double Life Ceiling Fan	C, C-9	3000	455			4.63	
		13369	●☀	40B13/DL/FAN/BL/2PK	120	12	Clear Double Life Ceiling Fan	C, C-9	3000	455			4.63	
G25	Med	14174	●☀	40G25/DL/1/48	120	48	Clear Double Life Globe	C, C-9	3000				4.44	
		14147	●☀	40G25/DL/RP	120	6	Clear Double Life Globe	C, C-9	3000				4.44	
		14148	●☀	40G25/DL/SW/RP	120	6	Soft White Double Life Globe	C, C-9	3000				4.44	
45	R20	Med Brass	15698	2,46,68,155	45R20/DL/RP	120	6	Double Life Reflector Flood	C, C-9	4000	260		3.94	
50 100 150	A21	3 CONTACT Med	18168	●▼	50150A21DL/SW/1/48	120	48	Soft White Double Life 3-way	C, CC-8	2400	540lm 1400lm 1940lm	3.38	5.31	
			18044	●▼	50/150A21/DL/SW/RP	120	12	Soft White Double Life 3-way	C, CC-8	2400	540lm 1400lm 1940lm	3.38	5.31	
50	R20	Med Brass	15346	2,46,68,107,155	50R20/DL/1/48	120	48	Double Life Reflector Flood	C, C-9	4000	290		3.94	
			14943	2,46,68,107,155	50R20/DL/RP	120	6	Double Life Reflector Flood	C, C-9	4000	290		3.94	



B10

B13

C15

F15

G16.5

DECORATIVE LAMPS

Watts	Bulb	Base	Product Number	Symbols & Footnotes	Ordering Abbreviation	Volts	Pkg Qty	Description	Class & Filament	Avg Rated Life(hrs)	MOL (in)	
40	B10	Candelabra	13571	●▼▲	40B10C/BAGPK	120	200	Clear Décor Bent Tip	C, C-7A	1500	3.88	
			13648	●▼▲	40B10C/BL/4PK	120	24	Clear Décor Bent Tip	C, C-7A	1500	3.88	
			13456	●▼▲	40B10C/BL/2PK	120	12	Clear Décor Bent Tip	C, C-7A	1500	3.88	
			13681	●▼▲	40B10C/T/BL/2PK	120	12	Clear Décor Blunt Tip	C, C-7A	1500	3.63	
			13714	●▼▲	40B10C/CRYSTAL/DL/BL/4/24	120	24	Double Life Crystal Bent Tip	C, C-7A	3000	3.88	
			13741	●▼▲	40B10C/CRYSTAL/DL/BL/2PK	120	12	Double Life Crystal Bent Tip	C, C-7A	3000	3.88	
			13309	●▼▲	40B10C/DL/F/BL/4PK	120	24	Frosted Double Life Décor Bent Tip	C, C-7A	3000	3.88	
			13320	●▼▲	40B10C/DL/F/BL/2PK	120	12	Frosted Double Life Décor Bent Tip	C, C-7A	3000	3.88	
			13457	●▼▲	40B10C/F/BL/2PK	120	12	Frosted Décor Bent Tip	C, C-7A	1500	3.88	
			13682	●▼▲	40B10C/F/T/BL/2PK	120	12	Frosted Décor Blunt Tip	C, C-7A	1500	3.63	
			Med	15354	●▼▲	40B10/DAY/2PK/BL	120	12	Daylight Décor Bent Tip	C, C-7A	1000	3.88
				13321	●▼▲ ⁹⁴	40B10/DL/BL/2PK	120	12	Clear Double Life Décor Bent Tip	C, C-7A	3000	3.81
	13651	●▼▲ ⁹⁴		40B10/BL/4PK	120	24	Clear Décor Bent Tip	C, C-7A	1500	3.81		
	13440	●▼▲ ⁹⁴		40B10/BL/2PK	120	12	Clear Décor Bent Tip	C, C-7A	1500	3.81		
	13719	●▼▲ ⁹⁴		40B10/T/BL/2PK	120	12	Clear Décor Blunt Tip	C, C-7A	1500	3.56		
	13723	●▼▲ ⁹⁴		40B10/CRYSTAL/DL/BL/4PK	120	24	Double Life Crystal Bent Tip	C, C-7A	3000	3.81		
	13740	●▼▲ ⁹⁴		40B10/CRYSTAL/DL/BL/2PK	120	12	Double Life Crystal Bent Tip	C, C-7A	3000	3.81		
	13322	●▼▲ ⁹⁴		40B10/DLF/BL/2PK	120	12	Frosted Double Life Décor Bent Tip	C, C-2V	3000	3.81		
	13441	●▼▲ ⁹⁴	40B10/F/BL/2PK	120	12	Frosted Décor Bent Tip	C, C-7A	1500	3.81			
	13720	●▼▲ ⁹⁴	40B10/F/T/BL/2PK	120	12	Frosted Décor Blunt Tip	C, C-7A	1500	3.56			
B13	Candelabra	13357	▲	40B13C/CL/FAN/2/12/BL	120	12	Clear Ceiling Fan Light	C, C-9	1500	4.00		
		Med	13366	●▲	40B13/DL/FAN/2/60/BL	120	60	Clear Double Life Ceiling Fan	C, C-9	3000	4.63	
	13369		●▲	40B13/DL/FAN/BL/2PK	120	12	Clear Double Life Ceiling Fan	C, C-9	3000	4.63		
	13367		●▲	40B13/FAN/BL/2PK	120	12	Clear Fan Lamp	C, C-9	1500	4.63		
	13786		●▲	40B13/CRYSTAL/FAN/4/72	120	72	Crystal Fan Lamp	C, C-9	1500	4.63		
	13785	●▲	40B13/CRYSTAL/FAN/BL/2PK	120	12	Crystal Fan Lamp	C, C-9	1500	4.63			
C15	Med	11691		40C15C/AM/SG/BL/1/6	120	6	Spun Glo Amber Fiber Wrap	C, C-9	1500	4.06		
F15	Med	13986	●▲	40F/AIC/BL/2PK	120	12	Amber Flame Shape Iridescent	C, C-7A	1500	4.50		
		13974	●▲	40F/CL	120	24	Clear Flame Shape	C, C-7A	1500	4.50		
		13985	●▲	40F/IC/BL/2PK	120	12	Iridescent Flame Shape	C, C-7A	1500	4.50		
		13984	●▲	40F/W/BL/2PK	120	12	White Flame Shape	C, C-7A	1500	4.50		
G16.5	Candelabra	10367	●▼▲	40G16.5C/DAY/2PK/BL	120	12	Daylight Globe	C, C-7A	1500	3.00		
		13702	●▼▲	40G16.5C	120	24	Clear Globe	C, C-7A	1500	3.00		
		13346	●▼▲	40G16.5C/4PK/BL	120	24	Clear Globe	C, C-7A	1500	3.00		