

Specification Data

Fixture Description:	Type
Project/Job:	
SYLVANIA lamp:	
SYLVANIA ballast:	
Notes:	

Ordering Information

Item Number	Ordering Abbreviation	Watts	Bulb	Base	Initial Lumens	Mean Lumens ¹	lm/W	Avg. Rated Life				CCT	CRI
								Instant Start 3 hrs/ start	Instant Start 12 hrs start	Programmed Rapid Start 3 hrs/ start	Programmed Rapid Start 12 hrs/ start		
4 foot													
21527	F032/830/XP/XL/EC03	32	T8	Med Bi-Pin	2950	2830	92	36,000	52,000	65,000	67,000	3000K	85
21576	F032/835/XP/XL/EC03	32	T8	Med Bi-Pin	2950	2830	92	36,000	52,000	65,000	67,000	3500K	85
21577	F032/841/XP/XL/EC03	32	T8	Med Bi-Pin	2950	2830	92	36,000	52,000	65,000	67,000	4100K	85
22002	F032/850/XP/XL/EC03	32	T8	Med Bi-Pin	2950	2830	92	36,000	52,000	65,000	67,000	5000K	81
21528	F028/830/XP/XL/SS/EC03	28	T8	Med Bi-Pin	2600	2470	93	50,000	75,000	80,000	84,000	3000K	85
22166	F028/835/XP/XL/SS/EC03	28	T8	Med Bi-Pin	2600	2470	93	50,000	75,000	80,000	84,000	3500K	85
22167	F028/841/XP/XL/SS/EC03	28	T8	Med Bi-Pin	2600	2470	93	50,000	75,000	80,000	84,000	4100K	85
22326	F028/850/XP/XL/SS/EC03	28	T8	Med Bi-Pin	2600	2470	93	50,000	75,000	80,000	84,000	5000K	81
22349	F032/25W/830/XP/XL/SS/EC03	25	T8	Med Bi-Pin	2400	2280	96	50,000	75,000	80,000	84,000	3000K	85
22222	F032/25W/835/XP/XL/SS/EC03	25	T8	Med Bi-Pin	2400	2280	96	50,000	75,000	80,000	84,000	3500K	85
22223	F032/25W/841/XP/XL/SS/EC03	25	T8	Med Bi-Pin	2400	2280	96	50,000	75,000	80,000	84,000	4100K	85
3 foot													
22493	F025/21W/830/XP/XL/SS/EC03	21	T8	Med Bi Pin	1850	1760	88	45,000	75,000	80,000	84,000	3000K	85
22494	F025/21W/835/XP/XL/SS/EC03	21	T8	Med Bi Pin	1850	1760	88	45,000	75,000	80,000	84,000	3500K	85
22495	F025/21W/841/XP/XL/SS/EC03	21	T8	Med Bi Pin	1850	1760	88	45,000	75,000	80,000	84,000	4100K	85
2 foot													
22490	F017/15W/830/XP/XL/SS/EC03	15	T8	Med Bi Pin	1150	1095	77	45,000	75,000	80,000	84,000	3000K	85
22491	F017/15W/835/XP/XL/SS/EC03	15	T8	Med Bi Pin	1150	1095	77	45,000	75,000	80,000	84,000	3500K	85
22492	F017/15W/841/XP/XL/SS/EC03	15	T8	Med Bi Pin	1150	1095	77	45,000	75,000	80,000	84,000	4100K	85

1. Measured at 40% of rated life.

Ordering Guide

FO	28	/	8	41	XP/XL	/	SS	/	EC03
Fluorescent OCTRON®	Wattage 15, 21, 25, 28, 32		CRI ≥ 81	Color Temperature 30 = 3000K 35 = 3500K 41 = 4100K 50 = 5000K	EXtended Performance EXtended Life		SUPERSAVER®		ECOLOGIC3

Lamp Dimensions

	(A) Max. Overall Length (in.)	(B) Base Face to Opposite Pin (in.)	(C) Max. Base Face to Base Face (in.)	(D) Max. Outside Diameter (in.)
F032, F028, F032/25W	47.78"	Min. 47.41" Max. 47.50"	47.22"	1.1"
F017	23.78"	Min. 23.41" Max. 23.50"	23.22"	1.1"
F025	35.78"	Min. 35.40" Max. 35.50"	35.22"	1.1"

