



LUMALUX PLUS® AND LUMALUX PLUS® ECO® Non-Cycling High Pressure Sodium

Watts	Bulb	Base	Product Number	Ordering Abbreviation	ANSI Code	Pkg Qty	Lamp Finish	Operating Position	Fix Req	Avg Rated Life (hrs)	Approx Lumens (initial)	Approx Lumens (mean)	CRI	CCT (K)	Symbols & Footnotes
100	E17	E26 Medium	67323	LU100/PLUS/MED	S54	20	Clear	Universal	0	30000	10000	9000	22	2100	☀️4,8
	ET23.5	E39 Mogul	67559	LU100/PLUS/ECO	S54	20	Clear	Universal	0	30000	10000	9000	22	2100	☀️4,7,8
150	ET23.5	E39 Mogul	67494	LU150/55/PLUS/ECO	S55	20	Clear	Universal	0	30000	16000	14400	22	2100	☀️4,7,8,13,36
200	ET18	E39 Mogul	67495	LU200/PLUS/ECO	S66	20	Clear	Universal	0	30000	22000	19800	22	2100	☀️4,7,8
250	ET18	E39 Mogul	67572	LU250/PLUS/ECO	S50	20	Clear	Universal	0	30000	29000	26100	22	2100	☀️4,7,8
310	ET18	E39 Mogul	67660	LU310/PLUS/ECO	S67	20	Clear	Universal	0	30000	37000	33300	22	2100	☀️4,7,8
400	ET18	E39 Mogul	67312	LU400/PLUS/ECO	S51	20	Clear	Universal	0	30000	50000	45000	22	2100	☀️4,7,8
1000	E25	E39 Mogul	67316	LU1000/PLUS	S52	6	Clear	Universal	0	30000	130000	124000	22	2100	☀️4,8

LUMALUX® STANDARD AND LUMALUX® ECO®

Watts	Bulb	Base	Product Number	Ordering Abbreviation	ANSI Code	Pkg Qty	Lamp Finish	Operating Position	Fix Req	Avg Rated Life (hrs)	Approx Lumens (initial)	Approx Lumens (mean)	CRI	CCT (K)	Symbols & Footnotes
35	E17	E26 Medium	67500	LU35/MED	S76	20	Clear	Universal	0	16000+	2250	2050	22	1900	4,22
			67501	LU35/D/MED	S76	20	Coated	Universal	0	16000+	2100	1935	22	1900	4,22
50	E17	E26 Medium	67502	LU50/MED	S68	20	Clear	Universal	0	24000+	4000	3600	21	1900	4,22
			67503	LU50/D/MED	S68	20	Coated	Universal	0	24000+	3700	3420	22	1900	4,22
	ET23.5	E39 Mogul	67510	LU50/ECO	S68	20	Clear	Universal	0	24000+	4000	3600	22	1900	☀️4,7,22
			67511	LU50/D	S68	20	Coated	Universal	0	24000+	3700	3420	22	1900	4,22
70	E17	E26 Medium	67504	LU70/MED	S62	20	Clear	Universal	0	24000+	6300	5350	22	1900	4,22
			67505	LU70/D/MED	S62	20	Coated	Universal	0	24000+	5800	4900	22	1900	4,22
	ET23.5	E39 Mogul	67512	LU70/ECO	S62	20	Clear	Universal	0	24000+	6300	5500	22	1900	☀️4,7,22
			67513	LU70/D	S62	20	Coated	Universal	0	24000+	5500	4900	22	1900	4,22
100	E17	E26 Medium	67506	LU100/MED	S54	20	Clear	Universal	0	24000+	9500	8000	22	2100	4,22
			67507	LU100/D/MED	S54	20	Coated	Universal	0	24000+	8800	7500	22	2100	4,22
	ET23.5	E39 Mogul	67514	LU100/ECO	S54	20	Clear	Universal	0	24000+	9500	8000	22	2100	☀️4,7,22
			67515	LU100/D	S54	20	Coated	Universal	0	24000+	8800	7500	22	2100	4,22
150	E17	E26 Medium	67508	LU150/55/MED	S55	20	Clear	Universal	0	24000+	15800	13400	22	2100	4,13,22,36
			67509	LU150/55/D/MED	S55	20	Coated	Universal	0	24000+	14500	12300	22	2100	4,13,22,36
	ET23.5	E39 Mogul	67516	LU150/55/ECO	S55	20	Clear	Universal	0	24000+	16000	13800	22	2100	☀️4,7,13,22,36
			67517	LU150/55/D	S55	20	Coated	Universal	0	24000+	14000	12500	22	2100	4,13,22,36
	BT28	E39 Mogul	67518	LU150/100	S56	10	Clear	Universal	0	24000+	15700	14100	22	2100	4,14,22,36
200	ET18	E39 Mogul	67576	LU200/ECO	S66	20	Clear	Universal	0	24000+	22000	19800	22	2100	☀️4,7,22
250	ET18	E39 Mogul	67578	LU250/ECO	S50	20	Clear	Universal	0	24000+	29000	26100	22	2100	☀️4,7,22
	BT28	E39 Mogul	67521	LU250/D	S50	10	Coated	Universal	0	24000+	26000	23400	22	2100	4,22
310	ET18	E39 Mogul	67580	LU310/ECO	S67	20	Clear	Universal	0	24000+	37000	32300	22	2100	☀️4,7,22
400	ET18	E39 Mogul	67533	LU400/ECO	S51	20	Clear	Universal	0	24000+	50000	45000	22	2100	☀️4,7,22
	BT37	E39 Mogul	67524	LU400/D	S51	10	Coated	Universal	0	24000+	47500	40000	22	2100	4,22
600	T14.5	E40 Mogul	67610	LU600 SUPER	S106	12	Clear	Universal	0	24000	90000	81000	25	2200	3
750	BT37	E39 Mogul	67547	LU750	S111	6	Clear	Universal	0	24000+	105000	94500	22	2100	3,22
1000	E25	E39 Mogul	67307	LU1000/ECO	S52	6	Clear	Universal	0	24000+	130000	124000	22	2100	3,22