



DULUX® EL Twist

DULUX® EL SELF-BALLASTED COMPACT FLUORESCENT LAMPS

Mini Twist Compact Fluorescent Lamps

Nominal Wattage	Bulb	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Avg Rated Life (hrs)	CCT (K)	CRI	Approx Lumens Initial @25°C/77°F	Approx Lumens Mean	Symbols & Footnotes
13	MINITWIST	4.6	Medium	29727	CF13EL/MICRO/830/RP2	120	12	12000	3000	82	825	660	1,3,8, 9,12,14,20
		4.5	Medium	29376	CF13EL/MINI/830	120	6	8000	3000	82	800	640	1,3,8, 9,12,14,20
		4.2	Medium	29059	CF13EL/SUPER/827/BL	120	6	10000	2700	82	880	704	1,3,8, 9,12,14,20
				29449	CF13EL/SUPER/830/BL	120	6	10000	3000	82	880	704	1,3,8, 9,12,14,20
				29713	CF13EL/SUPER/835/BL	120	6	10000	3500	82	800	640	1,3,8, 9,12,14,20
		4.6	Medium	29567	CF13EL/MINI/841	120	6	10000	4100	82	800	640	1,3,8, 9,12,14,20
		4.2	Medium	29588	CF13EL/SUPER/850/BL	120	10	10000	5000	82	800	640	1,3,8, 9,12,14,20
29469	CF13EL/MINI/865/BL/CS10			120	10	10000	6500	82	800	640	1,3,8, 9,12,14,20		
19	MINITWIST	5.2	Medium	29410	CF19EL/MINI/827	120	6	8000	2700	82	1200	960	1,3,8, 9,12,14,20
		5.5	Medium	29396	CF19EL/MINI/830	120	6	8000	3000	82	1200	960	1,3,8, 9,12,14,20
		4.7	Medium	29689	CF19EL/SUPER/830/BL	120	6	10000	3000	82	1200	960	1,3,8, 9,12,14,20
				28950	CF19EL/SUPER/850/BL	120	6	10000	5000	82	1200	960	1,3,8, 9,12,14,20
				29720	CF19EL/SUPER/865/BL	120	6	10000	6500	82	1200	960	1,3,8, 9,12,14,20
20	MINITWIST	4.2	Medium	29728	CF20EL/MICRO/830/RP2	120	12	12000	3000	82	1280	1024	1,3,8, 9,12,14,20
23	MINITWIST	4.6	Medium	29411	CF23EL/MINI/827	120	6	10000	2700	82	1600	1280	1,3,8, 9,12,14,20
		4.4	Medium	29729	CF23EL/MICRO/830/RP2	120	12	12000	3000	82	1600	1280	1,3,8, 9,12,14,20
		5.75	Medium	29397	CF23EL/MINI/830	120	6	8000	3000	82	1600	1280	1,3,8, 9,12,14,20
		5.06	Medium	29692	CF23EL/SUPER/830/BL	120	6	10000	3000	82	1600	1280	1,3,8, 9,12,14,20
				29714	CF23EL/SUPER/835/BL	120	6	10000	3500	82	1600	1280	1,3,8, 9,12,14,20
		4.6	Medium	29564	CF23EL/MINI/841	120	6	10000	4100	82	1600	1280	1,3,8, 9,12,14,20
		5.06	Medium	29690	CF23EL/SUPER/850/BL	120	6	10000	5000	82	1600	1280	1,3,8, 9,12,14,20
				29716	CF23EL/SUPER/865/BL	120	6	10000	6500	82	1600	1280	1,3,8, 9,12,14,20
30	MINITWIST	4.93	Medium	29578	CF30EL/MINI/835/DAY/BL	120	5	6000	3500	82	2000	1600	1,3,8, 9,12,14,20