



T6.5



A19



R14 Inter



R14



T8



T10

GENERAL PURPOSE LAMPS

Watts	Bulb	Base	Product Number	Symbols & Footnotes	Ordering Abbreviation	Volts	Pkg Qty	Description	Class & Filament	Avg Rated Life (hrs)	Lumens Beam Angle CBCP	LCL (in)	MOL (in)	
20	T6.5	DC Bayonet	18144	1	20T6.5DC/IF	120	60	Inside Frost Exit Lamp	B, C-8	10000	92		5.56	
			18143	1	20T6.5/IF	120	60	Inside Frost Exit Lamp	B, C-8	10000	92		5.50	
25	A19	Med	11090	●	25A/RS	120	120	Inside Frost Rough Service	B, C-17	1000	210	2.50	3.94	
			11092	●	25A/RS	130	120	Inside Frost Rough Service	B, C-17	1000	210	2.50	3.94	
			10562	●	25A/W/RP	120	24	Soft White	C, C-9	2500	160	2.50	3.94	
			10644	●	25A	120	120	Standard Frost	B, C-9	2500	190	2.50	3.94	
			10634	●	25A/RP	120	24	Standard Frost	B, C-9	2500	190	2.50	3.94	
			10645	● ^{136,146}	25A <i>@120_volts, approximate 22 watts, 130 lumens, 6250 hours</i>	130	120	Standard Frost	B, C-9	2500	180	2.50	3.94	
			11285	●	25A	230	120	Standard Frost	B, C-17	1000	205	2.50	3.94	
			11289	●	25A	277	120	Standard Frost	B, C-17	1000	187	2.50	3.94	
			Med Brass	10693		25A/CL	120	120	Clear	B, C-9	2500	190	2.50	3.94
				10683		25A/CL/RP	120	24	Clear	B, C-9	2500	190	2.50	3.94
				10694	^{136,146}	25A/CL <i>@120_volts, approximate 22 watts, 130 lumens, 6250 hours</i>	130	120	Clear	B, C-9	2500	180	2.50	3.94
				11710		25A19/TB/RP	125	6	Transparent Blue	B, C-9	3000		2.50	3.94
				11714		25A19/TG/RP	125	6	Transparent Green	B, C-9	3000		2.50	3.94
				11711		25A19/TO/RP	125	6	Transparent Orange	B, C-9	3000		2.50	3.94
				11712		25A19/TR/RP	125	6	Transparent Red	B, C-9	3000		2.50	3.94
				11713		25A19/TY/RP	125	6	Transparent Yellow	B, C-9	3000		2.50	3.94
10449		25A		12	120	Standard Frost	B, C-6	1000	385	2.50	3.94			
R14	Intermediate	14793		●	25R14N	120	60	Reflector Mini Flood	B, CC-2V	1500	132		2.56	
		14784	●	25R14N/RP	120	6	Reflector Mini Flood	B, CC-2V	1500	132		2.56		
	Med	14818	●	25R14/RP	120	6	Reflector Mini Flood	C, CC-2V	1500	132		2.25		
T6.5	DC Bayonet	18129		25T6.5/DC	120	60	Clear Scale Illuminator	B, C-8	1000	242		5.56		
		18106		25T6.5/DC	130	60	Clear Scale Illuminator	B, C-8	1000	242		5.56		
		18117		25T6.5/DC/IF	120	60	Inside Frost Scale Illuminator	B, C-8	1000	225		5.56		
	Intermediate	18125		25T6.5	120	60	Clear	B, C-8	1000	242		5.50		
		18496		25T6.5/CL/BL/10PK	120	10	Clear	B, C-8	1000	242		5.50		
		18495		25T6.5/BL/6PK	120	6	Clear	B, C-8	1000	242		5.50		
		18128		25T6.5	130	60	Clear	B, C-8	1000	242		5.50		
		18113		25T6.5/IF	120	60	Inside Frost	B, C-8	1000	225		5.50		
18111		25T6.5/IF	130	60	Inside Frost	B, C-8	1000	225		5.50				
T8	Candelabra	18289	●111	25T8C	120	60	Clear Home Appliance	B, C-7A	1000	230	1.50	2.63		
		DC Bayonet	18310	111	25T8DC	120	60	Clear Home Appliance	B, C-7A	1000	230	1.31	2.63	
	Intermediate	18321	111	25T8DC/BL	120	12	Clear Home Appliance	B, C-7A	1000	230	1.31	2.63		
		18316	111	25T8DC	130	60	Clear Home Appliance	B, C-7A	1000	215	1.31	2.63		
		18359	111	25T8N	120	60	Clear Home Appliance	B, C-7A	1000	230	1.31	2.63		
	18365	111	25T8N/BL	120	12	Clear Home Appliance	B, C-7A	1000	230	1.31	2.63			
	18360	111	25T8N/BL/1/6	120	6	Clear Home Appliance	B, C-7A	1000	230	1.31	2.63			
T10	Med	18510	●	25T10	120	60	Clear	B, C-8	1000	232		5.63		