

INSTANT START LAMPS

Slimline Standard Instant Start Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	CRI	Approx Lumens		Symbols & Footnotes
											Initial @25°C/77°F	Mean	
39	T12	48	46	Single Pin	24834	F48T12/D	30	9000	6500	76	2450	2156	31,33,48
					24836	F48T12D/ECO	30	9000	6500	76	2450	2156	31,33,48,76
50	T12	60	58	Single Pin	26018	F60T12/D35	30	12000	3500	70	3850	3542	31,33,48,97
					26001	F60T12/CW	30	12000	4200	60	3700	3256	31,33,48,97
					26002	F60T12/D	30	12000	6500	76	3000	2640	31,33,48,97
51	T8	96	94	Single Pin	29666	F96T8/CW	24	7500	4200	60	4000	3520	31,33,48
					29650	F96T8/D	24	7500	6500	76	3550	3124	31,33,48
52	T12	64	62	Single Pin	26403	F64T12/CW	30	12000	4200	60	3900	3432	31,33,48,97
					26404	F64T12/D	30	12000	6500	76	3300	2904	31,33,48,97
55	T12	72	70	Single Pin	27255	F72T12/D830	15	12000	3000	80	4800	4512	31,33,48,97
					27250	F72T12/D35	15	12000	3500	70	4700	4324	31,33,48,97
					27243	F72T12/D41	15	12000	4100	70	4700	4324	31,33,48,97
					27256	F72T12/CW	15	12000	4200	60	4500	3960	31,33,48,97
					27259	F72T12/D	15	12000	6500	76	3800	3432	31,33,48,97
70	T12	84	82	Single Pin	28417	F84T12/CW	15	12000	4200	60	5300	4664	31,33,48,97
75	T12	96	94	Single Pin	29796	F96T12/D30/ECO	15	12000	3000	70	6420	5906	31,33,48,76,97
					29827	F96T12/D830	15	12000	3000	80	6550	6157	31,33,48,97
					29856	F96T12/D830/ECO	15	12000	3000	80	6550	6157	31,33,48,76,97
					29685	F96T12/D35	15	12000	3500	70	6420	5906	31,33,48,97
					29686	F96T12/D35/ECO	15	12000	3500	70	6420	5906	31,33,48,76,97
					29843	F96T12/D835	15	12000	3500	80	6550	6157	31,33,48,97
					29838	F96T12/D835/ECO	15	12000	3500	80	6550	6157	31,33,48,76,97
					29797	F96T12/D41/CVP	10	12000	4100	70	6420	5906	31,33,48,97
					29478	F96T12/CWX	15	12000	4100	87	4400	3872	31,33,48,97
					29858	F96T12/CWX/CVP	10	12000	4100	87	4400	3872	31,33,48,97
					29489	F96T12/CWX/UPC	15	12000	4100	87	4400	3872	31,33,48,97
					29852	F96T12/D41/UPC	15	12000	4100	70	6420	5906	31,33,48,97
					29798	F96T12/D41/ECO	15	12000	4100	70	6420	5906	31,33,48,76,97
					29857	F96T12/D841	15	12000	4100	80	6550	6157	31,33,48,97
					29850	F96T12/D841/ECO	15	12000	4100	80	6550	6157	31,33,48,76,97
					29833	F96T12/DSGN50	15	12000	5000	90	4400	3872	31,33,48,97
					29849	F96T12/D865	15	12000	6500	80	6000	5520	31,33,48,97
29500	F96T12/DX	15	12000	6500	88	4360	3837	31,33,48,97					

FULL SPECTRUM